



PART NUMBER	REV	FIRST USED
680239-1	A	122500-1
680239-2	A	565435-5
680239-3	A	354500-1



- 1 RECOMMENDED SPARE PARTS.
- 2 GREASE LIGHTLY.
- 3 GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE.
- 4 LUBRICATE DAILY USING NO. 20 MACHINE OIL.
- 5. ITEMS WITH QTY OF REF SPECIFIED (EXCEPT ITEMS 78 AND 79) ARE USED ON ITEM 46.
- 6 CUT TO LENGTH AT ASSY.
- 7 FEED ADJUSTMENT NECESSARY WHEN CHANGING TERMINALS.

TERMINAL NAME: Ø4 CONTACT SOCKET			
962868 962862		CRIMPING DATA	
PAD LTR	CRIMP HEIGHT		WIRE SIZE
	A .078 ±.002 [1.98 ±0.05mm]		2.5mm ²
	B .072 ±.002 [1.84 ±0.05mm]		2mm ²
	C .067 ±.002 [1.71 ±0.05mm]		1.5mm ²
D		NOT	USED
CRIMP		SIZE	TYPE
WIRE .100 [2.54mm]		F	1.5 - 2.5mm ²
INSUL .140 [3.556mm]		OV	2.10 - 3mm
WIRE STRIP LENGTH .203-.234		TERM APPL SPEC -	FEED .748 1.669
		APPL INSTRUCTION 408-8040	SET UP GAGE LAYOUT 458637-1 L1708

2	2	2	-	C	9-354778-4	PIN, WIRE DISC (.2965) C	129
2	2	2	-	C	8-354778-3	PIN, WIRE DISC (.2910) B	127
2	2	2	-	C	6-354778-9	PIN, WIRE DISC (.2840) A	126
1	1	1	-	A	986950-1	WASHER, FLAT PRECISION	125
1	1	1	-	A	217238-1	DOCUMENTATION PACKAGE	124
1	1	1	-	-	4088040	SF APPL INST 408-8040	123
							122
							121
REF	REF	REF	-	A	1-21030-1	PIN, DOWEL (Ø.187x.50) LEVER	120
REF	REF	REF	-	A	1-21030-6	PIN, DOWEL (Ø.187x1.25) HOUSING	119
REF	REF	REF	-	A	21045-3	RING, RET "C" (Ø.187) FD FING PIN	118
1	1	1	-	A	21024-5	WASHER, LOCK (#10) ADJ BLOCK	117
REF	REF	REF	-	A	21024-5	WASHER, LOCK (#10) ADJ PLATE	116
REF	REF	REF	-	A	21024-5	WASHER, LOCK (#10) FEED GDE ROD	115
2	2	2	-	A	21024-2	WASHER, LOCK (#4) FRONT STP GUIDE	114
REF	REF	REF	-	A	5-21028-1	PIN, SLT 5PR (Ø.125x.50) ADJ ROD	113
							112
4	4	4	-	A	21024-4	WASHER, LOCK (#8) STRIPPER	111
REF	REF	REF	-	A	21899-4	WASHER, FLAT (Ø5/16) SCREW ADJ	110
							109
1	1	1	-	A	21018-5	NUT, HEX (NO. 6) HOLDDOWN	108
REF	REF	REF	-	A	21018-5	NUT, HEX (6-32) FEED ADJ	107
							106
							105
1	1	-	-	A	992031-1	PIN, CLEVIS	104
1	1	1	-	A	21009-2	SCR, SKT SET (1/4-20x.25 LW) RAM	103
2	2	2	-	A	21017-2	SCR, DRIVE (#2x.19) ID PLATE	102
REF	REF	REF	-	A	6-23715-5	SCR, PAN HD (6-32x1.50) FEED ADJ	101
1	1	1	-	B	461264-1	PLATE, IDENTIFICATION	100
2	2	2	-	A	3-21002-0	SCR, BHC (10-32x.88) DRAG	99
1	1	1	-	A	22733-8	SCR, BHC (8-32x.38 LW) ANVIL	98
REF	REF	REF	-	A	2-21002-9	SCR, BHC (10-32x.75) CAP	97
REF	REF	REF	-	A	2-22733-8	SCR, BHC (1/4-20x.62) HOUSING	96
REF	REF	REF	-	A	2-21002-7	SCR, BHC (10-32x.50) SG ADJ BLOCK	95
6	6	6	-	A	2-21002-2	SCR, BHC (8-32x.50) TERM H DWN	94
							93
							92
1	1	1	-	A	1-21002-7	SCR, BHC (6-32x.38) CAM	91
							90
1	1	-	-	A	7-21000-9	SCR, SHC (4-40x.19) STRIPPER	89
							88
2	2	2	-	A	2-21000-7	SCR, SHC (8-32x.49) DEP-HOLD	87
1	1	1	-	A	2-22603-0	SCR, HEX HD (8-32x.31) FEED FINGER	86
2	2	2	-	A	1-21000-3	SCR, SHC (4-40x.25) F ST GUIDE	85
1	1	1	-	A	2-21000-7	SCR, SHC (8-32x.50) STRIPPER	84
REF	REF	REF	-	A	3-21000-7	SCR, SHC (10-32x.75) FEED ROD GD	83
REF	REF	REF	-	A	3-21000-6	SCR, SHC (10-32x.62) FD ADJ BLK	82
1	1	1	-	A	3-21000-4	SCR, SHC (10-32x.38) SG ADJ BL	81
REF	REF	REF	-	A	3-21000-4	SCR, SHC (10-32x.38) PIVOT BLK	80
-	REF	-	-	B	455749-1	GUARD, WINDOW	79
REF	-	-	-	B	679532-1	INSERT, GUARD	78
							77
							76
							75
1	1	1	-	A	690603-1	SPRING, ASSIST	74
1	1	1	-	A	23030-1	SCR, SHC (6-32x.25 SL) INS DISC	73
REF	REF	REF	-	A	458109-1	WASHER, SPECIAL	72
REF	REF	REF	-	A	690517-1	SPACER	71
-3	-2	-1	U/M	DWG SIZE	PART NO	DESCRIPTION	ITEM NO
QTY RECD PER ASSY				PARTS LIST			

-1					LEADMAKER		MECH POST FEED		
-2					BENCH MODEL K		MECH PRE FEED		
-3					BENCH MODEL G		MECH PRE FEED		
REF	REF	REF	-	B	22594-8	NUT, HEX (1/2-20)	70		
REF	REF	REF	-	B	240628-1	PLATE, ADJUSTMENT	69		
REF	REF	REF	-	B	240626-1	SHAFT, PIVOT	68		
REF	REF	REF	-	B	240633-1	BUSHING	67		
REF	REF	REF	-	A	455680-1	LEVER, INTERMEDIATE	66		
REF	REF	REF	-	B	240629-1	BLOCK, PIVOT	65		
REF	REF	REF	-	A	240632-2	SCREW, ADJ FEED ROD	64		
REF	REF	REF	-	B	240659-3	PIN, CAM ROLLER	63		
REF	REF	REF	-	B	240658-1	ROLLER, CAM	62		
REF	REF	REF	-	B	454398-2	ROD, FEED	61		
REF	REF	REF	-	A	454178-1	GUIDE, FEED ROD	60		
REF	REF	REF	-	C	454220-1	CAP, RAM	59		
REF	REF	REF	-	D	454485-1	HOUSING	58		
							57		
1	1	1	-	B	690542-2	PAWL, FEED	56		
REF	REF	REF	-	B	240624-1	PIN, FEED FINGER	55		
REF	REF	REF	-	B	691499-1	SPRING, FEED FINGER	54		
REF	REF	REF	-	B	690541-1	HOLDER, FEED FINGER	53		
REF	REF	REF	-	A	455679-2	LEVER, TERMINAL FEED ARM	52		
1	1	1	-	A	811242-2	BUMPER, HOLDDOWN	51		
1	1	1	-	A	690753-1	SPACER, TONKER	50		
1	-	-	-	B	690602-6	CAM, PRE-FEED 1 5/8 ST	49		
-	1	-	-	B	690602-5	CAM, PRE-FEED 1 1/8 ST	48		
-	-	1	-	B	690501-4	CAM, POST-FEED 1 5/8 ST	47		
1	1	1	-	B	459456-2	APPLICATOR, BASIC (SUBASSY)	46		
1	1	1	-	A	690191-1	PLUG, NYLON	45		
1	1	1	-	C	455673-1	RAM	44		
1	1	1	-	A	690125-1	WASHER, LAMINATED	43		
1	1	1	-	A	690124-1	WASHER, RAM	42		
1	1	1	-	A	7-21002-9	BOLT, CRIMPER(5/16x1.00)	41		
1	1	1	-	A	23241-6	BALL, STEEL	40		
1	1	1	-	A	690170-1	SPRING, COMPRESSION	39		
1	1	1	-	C	690142-1	DISC, INSULATION	38		
1	1	1	-	D	354777-1	WIRE DISC, PLASTIC	37		
1	1	1	-	A	22480-5	WASHER, SPRING	36		
1	1	1	-	B	690212-1	POST, RAM	35		
1	1	1	-	B	690786-4	SUPPORT, TERMINAL	34		
REF	REF	REF	-	D	455675-1	PLATE, BASE	33		
							32		
							31		
REF	REF	REF	-	B	455689-1	BLOCK, STRIP GUIDE ADJ	30		
1	1	1	-	C	318756-1	STRIP GUIDE PLATE ASSY	29		
1	1	1	-	C	1-455888-8	SPACER, FRONT SHEAR DEP	28		
2	2	2	-	A	1-22284-0	SPRING, DRAG	27		
1	1	1	-	B	690546-1	LEVER, DRAG RELEASE	26		
1	1	1	-	B	240792-1	DRAG, TERMINAL	25		
1	1	1	-	D	7-690440-4	GUIDE, STRIP (REAR)	24		
1	1	1	-	A	690438-1	GUIDE, STRIP (FRONT)	23		
-	-	1	-	B	690472-2	STRIPPER	22		
REF	REF	REF	-	A	4-22284-9	SPRING, FEED RETURN	21		
1	1	-	-	A	679218-1	STRIPPER WIRE STOP ASSY	20		
1	1	-	-	B	458949-1	STRIPPER	19		
							18		
							17		
1	1	1	-	B	318563-1	GUARD, CHIP, FRONT	16		
							15		
							14		
							13		
1	1	1	-	A	5-22280-0	SPRING, SHEAR	12		
1	1	1	-	B	690461-1	STOP, SHEAR	11		
1	1	1	-	C	690459-1	HOLDER, SHEAR (FRONT)	10		
1	1	1	-	C	1-454276-9	SHEAR, FLOAT (FRONT)	9		
1	1	1	-	C	6-189717-1	ANVIL	8		
							7		
							6		
1	1	1	-	C	1-455889-4	DEPRESSOR, SHEAR (FRONT)	5		
1	1	1	-	B	238011-5	SPACER, BLOCK CRIMPER	4		
1	1	1	-	C	854830-8	CRIMPER, INSULATION	3		
1	1	1	-	C	1-455888-0	SPACER, CRIMPER	2		
1	1	1	-	C	2-456407-0	CRIMPER, WIRE	1		
-3	-2	-1	U/M	DWG SIZE	PART NO	DESCRIPTION	ITEM NO		
					← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)				
QTY RECD PER ASSY					PARTS LIST				
DIMENSIONS IN INCHES. DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 2 PLC DEC ±.02 3 PLC DEC ±.02 4 PLC DEC ±.01 ANGLES ±.01 SURF TEXTURE: √ REMOVE BURRS, BREAK SHARP EDGES R.015 MAX					MATL		HT TR	FIN	
					-		-	-	
					-		-	-	
					-		-	-	
DR J.BAKER 1/5/96 APP T ELBIN CHK 1/5/96 C.ERISMAN REL -					AMP AMP Incorporated Horrieburg, PA 17105-3608				
NAME					SIDE FEED HDM APPLICATOR				
SCALE					680239				
D					SHEET 1 OF 1				
DWG NO					REV A				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[680239-2](#)