


Amps Pin. Config-uration Earth Hour Pos.


16	2P+E	6
16	3P+E	9
16	3P+N+E	9
32	2P+E	6
32	3P+E	9
32	3P+N+E	9
63	2P+E	6
63	3P+E	9
63	3P+N+E	9

PLUGS



Dimensions in mm				
A	No. Poles (+ E)	A	B	C Dmax
16	2	95	58	58 14
16	3	111	65	74 16.5
16	3+N	111	73	74 16.5
32	2,3	113	78	68 19.5
32	3+N	126	86	78 21.5
63	2,3,3+N	215	155	137 35


CONNECTORS



Dimensions in mm				
A	No. Poles (+ E)	A	B	Dmax
16	2	110	65	14
16	3	126	74	16.5
16	3+N	126	81	16.5
32	2,3	126	83	19.5
32	3+N	136	93	21.5
63	2,3,3+N	224	112	35

SOCKET OUTLETS ANGLED

SURFACE




Dimensions in mm									
A	No. Poles (+ E)	A	B	C	C1	D	E		
16	2	80	115	76	54	M20x1.5	64		
16	3	91	115	76	62	M20x1.5	72		
16	3+N	94	115	76	62	M20x1.5	72		
32	2,3	106	138	90	72	M25x1.5	83		
32	3+N	110	138	90	72	M25x1.5	83		
63	2,3	136	254	170	95	M32x1.5	107		

Top conduit or rear cable entry
Supplied with blank plug

SOCKET OUTLETS ANGLED

SURFACE




Dimensions in mm					
A	B	C	D	E	
16	110	110	134	85	60
32	160	160	140	135	110


With all round conduit entry

SOCKET OUTLETS TWIN ANGLED

SURFACE




Prewired		Unwired	
13144	13044		



Amps Pin. Config-uration Earth Hour Pos.


16	2P+E	6
32	2P+E	6
63	2P+E	6
63	3P+E	9
63	3P+N+E	9
125	2P+E	6
125	3P+E	9
125	3P+N+E	9

PLUGS



Dimensions in mm				
A	No. Poles (+ E)	A	B	C Dmax
16	2	109	66	75 15
32	2	132	88	89 23
63	2,3,3+N	230	114	170 38
125	2,3,3+N	290	130	230 49


CONNECTORS



Dimensions in mm				
A	No. Poles (+ E)	A	B	Dmax
16	2	130	66	15
32	2	152	88	23
63	2,3,3+N	248	111	38
125	2,3,3+N	302	122	49

SOCKET OUTLETS

SURFACE




Dimensions in mm				
A	No. Poles (+ E)	A	B	C E
125	2,3,3+N	510	210	230 204

Top & bottom conduit entries

SOCKET OUTLETS ANGLED

SURFACE




Dimensions in mm							
A	No. Poles (+ E)	A	B	C	E	F	G
16	2	133	130	80	120	71	111
32	2	140	143	80	120	71	111
63	2	255	215	150	136	129	124

Top & bottom conduit entries

SOCKET OUTLETS STRAIGHT

PANEL MOUNTING



Dimensions in mm										
A	No. Poles (+ E)	C	C1	D	D2	E	E1	H		
63	2,3,3+N	61	61	70	98	89	48	111		
125	2,3	71	71	88	115	100	58	122		


63A plugs and connectors include pilot pins & sleeves
125A plugs include pilot pins

NOTE *New Products

Dimensional drawings feature the most representative products. Small design changes may occur (over different voltages) from one product to another.
All products are available in minimum order quantities of one.


SOCKET OUTLETS STRAIGHT

PANEL MOUNTING




SOCKET OUTLETS ANGLED

PANEL MOUNTING




SWITCHSOCKET OUTLETS ANGLED

SURFACE




SWITCHSOCKET OUTLETS INTERLOCKED ANGLED

SURFACE




SWITCHSOCKET OUTLETS INTERLOCKED ANGLED

SURFACE



APPLIANCE INLETS ANGLED

SURFACE



9401 BLU	9501 BLU	9913 BLU		9610 BLU	9701 BLU
9406 BLU	9506 BLU	9919 BLU		9601 BLU	9705 BLU
9414 BLU	9514 BLU			9607 BLU	9710 BLU
9433 BLU	9533 BLU			9643 BLU	9733 BLU
9436 BLU	9537 BLU			9633 BLU	9735 BLU
9444 BLU	9542 BLU			9639 BLU	9740 BLU
9472 BLU					9775 BLU
				9664 BLU	
				9669 BLU	
				9321 BLU	

A No.	Dimensions in mm	Poles	C	C1	D	E	E1	H
(+ E)								
16 2	44	44	49	50	18	65		
16 3	52	52	59	50	18	75		
16 3+N	52	52	59	50	18	82		
32 2	61	61	65	62	28	85		
32 3	61	61	65	62	31	85		
32 3+N	61	61	65	62	31	94		
63 2	61	61	70	98	87	107		

A No.	Dimensions in mm	Poles	C	C1	D	E	E1	H
(+ E)								
16 2	55	55	63	43	38	72		
16 3	60	60	69	45	38	72		
16 3+N	66	66	78	46	40	80		
32 2	70	70	82	50	48	84		
32 3	70	70	82	50	48	85		
32 3+N	75	75	87	53	56	94		

A No.	Dimensions in mm	Poles	A	B	C	D	E	F	Fix.
(+ E)									Centres
16 2	101	112	156	95	139	101	101	95	
16 3	99	112	156	95	139	101	101	95	

A No.	Dimensions in mm	Poles	B	C	C1	E1	H
(+ E)							
16 3,3+N	135	165	91.5	125	198		
32 3,3+N	135	165	91.5	135	198		
63 3,3+N	165	201	91.5	183	228		

Aluminium Alloy enclosure
Will accept auxiliary contact eg. 6864
FL9 flange entry (16 amp + 32 amp)
FL 13 flange entry (63 amp)
Flange entries top & bottom supplied with cover plate & gland plate

A No.	Dimensions in mm	Poles	B	C	C1	E	E1	H
(+ E)								
16 2	168	91	125	M25x1.5	116	129		
32 2	168	91	125	M25x1.5	126	129		
63 2,3,3+N	206	132	152		168	168		


63 amp
FL 13 flange entry at top)
Supplied with cover plate and gland plate

A No.	Dimensions in mm	Poles	B	C	C1	D	E1	H
(+ E)								
16 2	64	76	54	M20x1.5	67	107		
16 3	72	76	62	M20x1.5	76	106		
16 3+N	72	76	62	M20x1.5	79	107		
32 2,3	82	90	72	M25x1.5	91	128		
32 3+N	82	90	72	M25x1.5	94	129		
63 2	107	170	95	M32x1.5	117	238		

Top conduit or rear cable entry
Supplied with blanking plate


SOCKET OUTLETS ANGLED

PANEL MOUNTING




SWITCHSOCKET OUTLETS INTERLOCKED

SURFACE




SWITCHSOCKET OUTLETS INTERLOCKED ANGLED

SURFACE




APPLIANCE INLET

SURFACE



APPLIANCE INLET ANGLED

SURFACE



9803 BLU*		9324 BLU*		
9866 BLU*	9654 BLU	9369 BLU*		
9825 BLU	9657 BLU	9355 BLU		9826 BLU
9581 BLU		9341 BLU		9830 BLU*
9591 BLU		9351 BLU		
	9688 BLU*		9883 BLU	
	9690 BLU*			
	9693 BLU*		9887 BLU*	

A No.	Dimensions in mm	Poles	C	C1	D	E	E1	H
(+ E)								
16 2	55	55	50	55	32	80		
32 2	70	70	80	60	50	100		
63 2,3,3+N	84	80	92	61	86	111		

A No.	Dimensions in mm	Poles	A	B	C	D	E	F
(+ E)								
32 2	118	225	101	208	143	255		
63 2	160	260	140	240	195	304		
125 2,3,3+N	230	440	204	440	240	510		

A No.	Dimensions in mm	Poles	A	B	C
(+ E)					
16 2	126	129	168		
32 2	136	129	168		
63 2,3,3+N	182	168	206		

With FL13 flange entry at top

A No.	Dimensions in mm	Poles	B	C	E1	H
(+ E)						
125 2,3+N	230	240	210	552		

A No.	Dimensions in mm	Poles	B	C	C1	E1	H	H1
(+ E)								
63 2,3	150	124	129	205	250	186		

A No.	Dimensions in mm	Poles	G	H
(+ E)				
32 2	7	8		
63 2	8	10		