


**Panel Mount Indicator, Non-Relampable
LED Technology
Mounting Hole, Ø 0.310"**



All dimensions are in inches



RoHS
COMPLIANT

Minimum panel thickness: 0.030"

6" leads with 1/2" strip are standard

Storage temperature	T _{STG} : -25°C - +80°C
Ambient temperature	T _A : -20°C - +60°C
Voltage tolerance	V _{OP} : ±10%

[illegible]

Body Material: Nylon, white
 Lens Material: Polycarbonate
 Bezel Material: Chrome
 Wire Gauge: 18 AWG
 Wire Strip: 1/2"
 Anode(+): Red lead

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.

Options: Additional options and lens styles available. Please contact Wamco for more information.

Drawn	SC	03/01/10	Panel Mount Indicators LED	Datasheet: WL-2191LX-XXX Series	Rev: 2
Checked	EB	03/01/10			
Approved	EB	03/02/10			