


FD-55111-C

HONEYWELL
PART NUMBER
78303

REV	DOCUMENT	CHANGED BY	CHECK
C	0070272	SBH 12OCT10	CMH

USING 3/32 HIGH CHARACTERS, MARK WITH HONEYWELL
PART NO., PRESSURE SETTING, DATE CODE AND
ELECTRICAL RATING AS FOLLOWS:
78303-X XXX 3 AMP-6V 1.5 AMP-12V



SM. TO: 78063, M-4266

NOTES:

1. SINGLE CIRCUIT NORMALLY CLOSED PRESSURE SWITCH.
2. OPENING RANGE 25-50 $\pm$ 4 PSI.
3. SEE SPEC. 99005 FOR MANUFACTURING SPEC.

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:

NO PLACES	X	$\pm$	-
ONE PLACE	.X	$\pm$	.020
TWO PLACES	.XX	$\pm$	.010
THREE PLACES	.XXX	$\pm$	.005
ANGLES	X	$\pm$	0° 30'

THIRD ANGLE PROJECTION



DRAWN	MRH	20MAR92
CHECK	-	-

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

Honeywell

TITLE PRESSURE SWITCH N.C.
SCREW TERMINALS
UL 5000 SERIES SWITCH

SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
B	E	-	78303	C

AUTOCAD

2D

SCALE 2:1

SHEET

1 OF 1