


Dimensions: mm (In)

**Mechanical Specifications:**

- Operation Force: 220 ± 65 gf
- Stroke: 1st $0.50 + 0.10 / - 0.05$ mm
- Operation Temperature: -25°C to $+70^{\circ}\text{C}$
- Storage Temperature: -30°C to $+80^{\circ}\text{C}$

Electrical Specifications:

- Electrical Life: 100,000 cycles
- Rating: 50mA, 12VDC
- Contact Resistance: 100mΩ max.
- Insulation Resistance: 100MΩ min. @ 100VDC
- Dielectric Strength: 100VAC/1 minute
- Contact Arrangement: 1 pole 1 throw

Materials:

- Cover: Stainless steel
- Base: LCP High-temp thermoplastic; Color: White
- Stem: LCP High-temp thermoplastic; Color: Black
- Contact disc: Stainless with silver cladding
- Terminal: Brass with silver plating

Note:

- RoHS compliant and process compatible with 260° solder.

Tactile Switch
101-TS4722R2200-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-TS4722R2200-EV](#)