


T1/E1/CEPT/ISDN-PRI SMT TRANSFORMERS



- Small surface mount package
- Isolation voltage: 1500 Vrms minimum
- Extended temperature range: -40°C to +85°C
- Designed to meet Return Loss requirements of ITU G.703



Electrical Specifications @ 25°C — Operating Temperature -40°C to 85°C

Part Number	Turns Ratio (Pri:Sec - ±2%)	OCL Pri @ 25°C (mH MIN)	L _L (μH MIN)	C _{ww} (pF MAX)	DCR Pri (Ω MAX)	DCR Sec (Ω MAX)
TX1281	1CT:1	2.0	1.2	65	2.7	2.7
TX1282	1.14CT:1	2.2	1.4	65	2.8	2.8
TX1283	1.35CT:1	2.0	1.4	65	2.7	2.0
TX1284	1.26CT:1	1.2	1.0	50	2.5	2.0




Mechanical

Schematic

TX12XX



SUGGESTED PAD LAYOUT



Weight038 grams
Tape & Reel 1000/reel
Tray80/tray
Dimensions: $\frac{\text{Inches}}{\text{mm}}$
Unless otherwise specified,
all tolerances are $\pm \frac{.010}{0.25}$

For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
U.S.A.
http://www.pulseeng.com
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 287 8998
FAX: 65 280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.