

Technical Data

Issue 07 February 2000

AT142 Cotton Cloth Protection Tape

General description

A close woven unbleached cotton cloth with a white, acid-free, aggressive pressure sensitive adhesive.

- Conformable to awkward shapes.
- Strong.
- Good abrasion resistance.
- Non-corrosive adhesive.
- Can be written on.
- Can be used for veterinary purposes.

Specification

Certification* to the following standards may be available on request.
DEF STAN 75-2.

Technical Details

Typical values

Thickness 0.22mm

Breaking Load 60 N/cm

Elongation 5%

Adhesion


Steel 2.0 N/cm
Self 2.0 N/cm

Water Extract

pH 6.5 to 7.5
Chloride Max. 0.05% as NaCl
Sulphate Max. 0.25% as Na₂SO₄

Service Temp -10°C to +60°C

Application Temp +10°C to +45°C



NOTE

Except where indicated otherwise, the above figures are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The Company reserves the right to improve products and any change in specification will result in a re-issue of the relevant 'Technical Data Sheet'. Customers should satisfy themselves that the tape is suitable for their requirements whether after such modifications or otherwise. Please check that you have the latest issue of the 'Technical Data Sheet'. All sizing and length tolerances are to British Standards. Before use the customer is advised to consult the Health & Safety Data Sheet produced by this company for this product, which is available on request.

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.

*Standard charge for certificate: £25.00.

 **ADVANCE**
adhesive tapes



AFERA



INVESTITOR IN PEOPLE

AFERA

Association des Fabricants Européens de
Rubans Auto-Adhésifs.

Advance Tapes International Limited, PO Box 122,
Abbey Meadows, Leicester, LE4 5RA.
Tel: 0116 251 0191. Fax: 0116 265 2046. www.advancetapes.com