

Single Row Terminal Blocks

Kulka® 411 GP Series

300 Volts AC/DC (Class B)



411 GP 06 PSB

Specifications:

- Base, Phenolic, 150°C (UL RTI)
- Open Back Design (Insulator Strip Required for Voltage Rating - see page 112)
- JJ (GDI-30F) Material Available
- Screws, #2-56 Binder Head, Phil-Slot, Brass
- Terminals, Plated Brass
- 1-23 Poles
- 1/4" Centers
- Wire Range With Wire Binding Screw
#18 - #20 AWG – 5 Amps
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

Kulka® Catalog #	# of poles	Dimensions	
		A	B
411 GP 01 PSB	1	0.75	0.50
411 GP 02 PSB	2	1.00	0.75
411 GP 03 PSB	3	1.25	1.00
411 GP 04 PSB	4	1.50	1.25
411 GP 05 PSB	5	1.75	1.50
411 GP 06 PSB	6	2.00	1.75
411 GP 07 PSB	7	2.25	2.00
411 GP 08 PSB	8	2.50	2.25
411 GP 09 PSB	9	2.75	2.50
411 GP 10 PSB	10	3.00	2.75
411 GP 11 PSB	11	3.25	3.00
411 GP 12 PSB	12	3.50	3.25
411 GP 13 PSB	13	3.75	3.50
411 GP 14 PSB	14	4.00	3.75
411 GP 15 PSB	15	4.25	4.00
411 GP 16 PSB	16	4.50	4.25
411 GP 17 PSB	17	4.75	4.50
411 GP 18 PSB	18	5.00	4.75
411 GP 19 PSB	19	5.25	5.00
411 GP 20 PSB	20	5.50	5.25
411 GP 21 PSB	21	5.75	5.50
411 GP 22 PSB	22	6.00	5.75
411 GP 23 PSB	23	6.25	6.00

mm = dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG #	PRODUCT DESCRIPTION	PAGE REFERENCE
MSP	KULKA	
KT10	Full Quick Connect (0° Flat)	See page 104
KT11	Full Quick Connect (45° Bend)	See page 104
KT12	Full Quick Connect (90° Bend)	See page 104
KT16	Half Quick Connect (0° Flat)	See page 104
KT17	Half Quick Connect (45° Bend)	See page 104
KT18	Half Quick Connect (90° Bend)	See page 104
ST	Full Solder	See page 106
3/4 ST	Half Solder	See page 106
Z	Lug over the Side (.312)	Consult C/S
J 410	Line to Line Jumper	See page 107
1921	Printed Circuit Pin (.125) (Over the Side)	Consult C/S
1904	Feed Thru Solder	Consult C/S

Quick Connects: .020" x .110"

See pages 104-115 for terminal block accessories

