

MODULAR JACKS AND PLUGS: GAX Series

Right Angle Ganged Jack

Product Features

Available in 6 and 8 Position Housings
 Right Angle Version
 Ribbed Pin Guides
 Metal Locking Brackets
 CSA/NRTL Certified File No. LR78160

Performance Specifications

Materials and Finish

Housing Material

Thermoplastic, UL 94V-0 Rated, Gray Color

Contact Material

Phosphor Bronze

Electrical Characteristics

Insulation Resistance

500 Megohms Min.

Dielectric Withstanding Voltage

1000V AC RMS for 1 Minute

Contact Resistance

20 milliohms Max.

Current Rating

1.5A

Voltage Rating

125V DC

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-			
Series		No. of Ports	No. of Positions	Plating Option

Series

GAX - Right Angle PCB Mount

Number of Ports

2 - 2 Port
 3 - 3 Port
 4 - 4 Port
 5 - 5 Port (Available Only With 6 Positions)
 6 - 6 Port (Available Only With 6 Positions)
 7 - 7 Port (Available Only With 6 Positions)
 8 - 8 Port (Available Only With 6 Positions)

Number of Positions / Contacts

62 - 6 Positions / 2 Contacts
 64 - 6 Positions / 4 Contacts
 66 - 6 Positions / 6 Contacts
 88 - 8 Positions / 8 Contacts


Plating Option

Blank - Gold Flash
 50 - 50μ" Gold Plating

Contact Kycon for Other Options

GAX Series

Dimensions in mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kycon:

[GAX-8-66-50](#) [GAX-7-66-50](#) [GAX-3-66-50](#) [GAX-5-66-50](#) [GAX-4-66-50](#) [GAX-6-66-50](#) [GAX-2-66-50](#) [GAX-7-62-50](#)
[GAX-7-62](#) [GAX-7-66](#) [GAX-7-64](#) [GAX-6-64](#) [GAX-6-66](#) [GAX-8-64](#) [GAX-8-62](#) [GAX-8-66](#) [GAX-8-64-50](#) [GAX-5-64](#)
[GAX-5-66](#) [GAX-8-62-50](#) [GAX-2-64-50](#) [GAX-6-64-50](#) [GAX-4-64-50](#) [GAX-7-64-50](#) [GAX-3-64-50](#) [GAX-5-64-50](#) [GAX-](#)
[3-88-50](#) [GAX-4-88-50](#) [GAX-2-88-50](#) [GAX-3-88](#) [GAX-3-66](#) [GAX-3-64](#) [GAX-2-88](#) [GAX-2-64](#) [GAX-2-66](#) [GAX-8-62-](#)
[50-BLK](#) [GAX-4-88](#) [GAX-4-62](#) [GAX-4-66](#) [GAX-4-64](#) [GAX-2-62](#) [GAX-2-62-50](#) [GAX-2-62-50-BLK](#) [GAX-2-64-50-BLK](#)
[GAX-2-66-50-BLK](#) [GAX-3-62](#) [GAX-3-62-50](#) [GAX-4-62-50](#) [GAX-4-62-50-BLK](#) [GAX-4-62-BLK](#) [GAX-4-88K](#) [GAX-5-62](#)
[GAX-5-62-50](#) [GAX-6-62](#) [GAX-6-62-50](#) [GAX-2-62-BLK](#) [GAX-4-64-BLK](#) [GAX-8-62-BLK](#)