



REV.	DESCRIPTION	DATE
A	NEW DRAWING	1/18/2006




PCB LAYOUT
TOP VIEW

SPECIFICATIONS:
 RATING: 12V DC @ 1A
 CONTACT RESISTANCE: 100m OHMS MAX
 INSULATION RESISTANCE: 100M OHMS MIN: 500V DC
 VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE
 LIFE: 5,000 CYCLES
 OPERATING TEMP: -25° ~ +85°C

MODEL NO.	MJ1-2503A
SCHEMATIC	

TERMINAL 1	MATERIAL	PLATING
TERMINAL 2	Brass	Tin
TERMINAL 3	Copper Alloy	Tin
BUSHING	Copper Alloy	Tin
HOUSING	Brass	Nickel
	PBT	



TOLERANCE:
 X.X ±0.2mm
 X.XX ±0.1mm
 X.XXX ±0.05mm

CUI INC

20050 SW 112th Ave.
 Tualatin, OR 97062
 Phone: 503-643-4899
 800-275-4899
 Fax: 503-372-1266
 Website: www.cui.com

TITLE: 2.5mm PHONE JACK	REV: A
PART NO: MJ1-2503A	UNITS: MM [INCHES]
DRAWN BY: ZRJ	APPROVED BY:
	SCALE: 4:1