






SPECIFICATION:

- Bandwidth : 10Hz to 50KHz ± 3 dB
- Impedance : 600:600 ohms (Audio) , unbalanced to balanced
- Connectors : one RCA to one IDC
- Isolation : 500 V
- Nominal Level : 1.0 volts
- Insertion Loss : ≤ 1 dB
- Common Mode Rejection: Greater than 40 dB
- Cable-UTP : UTP:24 AWG or lower solid copper
UTP : Impedance: 100 ohms at 1MHz
Max. Capacitance: 20 pf/ft
Attenuation: 6.6 dB/1000 ft at 1 MHz
- Max. Distance : 2500feet (Cat.6)
- Temperature : Operating: 0° to 55° C
Storage: -20° to 85° C
Humidity: up to 95%

NOTE:

Right channel Audio , Red RCA Female to
Toolless IDC, for Keystone mounting



5	PCB SET (TRANSFORMER 1:1)	1 Set	
4	TOOLLESS IDC	1 Set	
3	PLASTIC HOUSING	1 Set	
2	RCA Keystone Housing	1 Set	
1	RCA FEMALE SOLDER TYPE (COLOR: Red insert in RCA Female)	1 Set	
NO.	DESCRIPTION	Q'TY	NOTE

DIMENSIONS ARE IN mm (INCH)	TOLERANCES ARE FRACTIONS DECIMALS ANGLES	MATERIAL
MOLD NO.	.X ± 0.25 .XX ± 0.10	FINISH
50-7760		COLOR

RIGHT AUDIO RCA BALUN,
KEYSTONE MOUNT, RED

P/N	50-7760	DRAWN	DATE 12/16/2005
PROJECT NO.			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	