



Sample photo

Order symbol: PC 17/16-LC3
Product nbr: 7520104
Description: Enclosure, PC
Remarks: Without main cover

EAN: 6418074039309
El. number:
Finland: 3421680
Denmark: 8212016635

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		166	160	80	Ingress Protection (EN 60529): IP 65
inch:		6.5	6.3	3.1	Impact Resistance (EN 62262): IK 08/07
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Gasket material:		EPDM			Flammability Rating (UL 746 C 5): UL 746C 5V
Temperatures:					Glow Wire Test (IEC 695-2-1) °C: 960
Short term:		-40 ... 120 °C			NEMA Class: NEMA 1, 3, 3R, 12, 13
Continuous:		-40 ... 80 °C			Certificates:
Short term:		-40 ... 250 °F			Underwriters Laboratories
Continuous:		-40 ... 175 °F			Fimko
Accessories:					Europe EN 62208: 2003
MP 17/16		Mounting plate			UL Canada
FP 17/16		Front plate (aluminium)			Gost R
FC PC 17/16		Frame of PC front plate			

