

**(1,27mm) .050"**

## DWM, HDWM SERIES



HDWM-20-58-G-S-427

HDWM-24-59-L-S-300-SM

DWM-08-56-L-D-312-SM

DWM-06-54-G-D-360

# MICRO BOARD STACKER

## SPECIFICATIONS

## DWM

For complete specifications  
see [www.samtec.com?DWM](http://www.samtec.com?DWM)

**Insulator Material:**

Top: Black LCP  
Bottom: Natural LCP

**Terminal Material:**

Phosphor Bronze

### Plating:

Au or Sn over

50μ" (1,27μm) Ni

**Current Rating:**

1A

**Operating Temp Range:**  
55°C to 125°C with Time

-55°C to +105°C V  
-55°C to +125°C V

-55  
Rol  
Yes

## HDWM

For complete specifications  
see [www.samtec.com?HDWM](http://www.samtec.com?HDWM)

Same as DWM except not CSA rated.


### Processing:

### Processing.

**Lead-Free Solderable:**

**SMT Lead Coplanarity:**  
(0,15mm) .006" max

**Mates with:**  
SMS, SLM, RSM

Variable  
stacker  
height

*Ideal for high density  
"skyscraper"  
board stacking*

Choice of Surface mount or Through-hole

| TYPE STRIP | NO. PINS PER ROW                                                                                                                           | LEAD STYLE                    | PLATING OPTION                                                                                                                          | ROW OPTION                                                 | STACKER HEIGHT                                                        | OTHER OPTION                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|------------|--------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------|-----------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|            | 01 thru 50                                                                                                                                 | Specify LEAD STYLE from chart | <b>-L</b><br>= 10μ" (0,25μm)<br>Gold contact, Matte Tin on tail<br><br><b>-G</b><br>= 10μ" (0,25μm)<br>Gold on post, Gold flash on tail | <b>-S</b><br>= Single Row<br><br><b>-D</b><br>= Double Row | <b>"XXX"</b><br>= Stacker Height Example:<br>-250 = (6,35mm)<br>.250" | <b>"XXX"</b><br>= Polarized Position (Specify position of omitted pin)<br><br><b>-SM</b><br>= Surface Mount (Requires HDWM. 02 thru 40 positions only.)<br><br><b>-A</b><br>= Alignment Pin (Requires HDWM. 6 positions min -D only.)<br>Metal or plastic at Samtec discretion (N/A with -LC)<br><br><b>-LC</b><br>= Locking Clip (Requires HDWM. 5 positions min. -D only.)<br>(Manual placement required)<br><br><b>-P</b><br>= Pick & Place Pad (Requires HDWM) |
|            | <div> <div> <b>DWM</b><br/>= Standard Board Spacer<br/><br/> <b>HDWM</b><br/>= High Temp Board Spacer           </div> <div> </div> </div> |                               |                                                                                                                                         |                                                            |                                                                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |

| LEAD STYLE | OAL           |               |
|------------|---------------|---------------|
|            | THROUGH-HOLE  | SURFACE MOUNT |
| -01        | (11,43) .450  | (8,38) .330   |
| -51        | (10,41) .410  | —             |
| -52        | (10,80) .425  | —             |
| -53        | (12,83) .505  | (9,78) .385   |
| -54        | (14,10) .555  | (11,05) .435  |
| -55        | (15,49) .610  | (12,45) .490  |
| -56        | (15,88) .625  | (12,83) .505  |
| -57        | (16,51) .650  | (13,46) .530  |
| -58        | (17,91) .705  | (14,86) .585  |
| -59        | (19,18) .755  | (15,62) .615  |
| -60        | (20,96) .825  | —             |
| -61        | (26,67) 1.050 | —             |

**Note:** Other Gold plating options available.  
Contact Samtec.

**Note:** These Series are non-standard, non-returnable.

*Due to technical progress, all designs, specifications and components are subject to change without notice*

**WWW.SAMTEC.COM**

**SAMTEC USA** • Tel: 1-800-SAMTEC-9 or 812-944-6733    **SAMTEC SILICON VALLEY** • Tel: 408-395-5900    **SAMTEC SOUTHERN CALIFORNIA** • Tel: 1-800-726-8329  
**SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA.** • Tel: (+55 31) 3786 3227    **SAMTEC UNITED KINGDOM** • Tel: 44 419 236 739292    **SAMTEC GERMANY** • Tel: 49 (0) 89 / 89460-0  
**SAMTEC FRANCE** • Tel: 33 01 60 95 06 60    **SAMTEC ITALY** • Tel: 39 039 6890337    **SAMTEC NORDIC/BALTIC** • Tel: +46-84477280    **SAMTEC BENELUX** • Tel: 44 236 739292  
**SAMTEC ISRAEL** • Tel: 972-3-7526600    **SAMTEC INDIA** • Tel: +91-80-3272 1612    **SAMTEC ASIA PACIFIC** • Tel: 65 6745-5955    **SAMTEC JAPAN** • Tel: 045-475-185    **SAMTEC CHINA** • Tel: 86-21-6083 3766  
**SAMTEC TAIWAN** • Tel: 886-2-2735-6109    **SAMTEC HONG KONG** • Tel: 852-26904858    **SAMTEC KOREA** • Tel: 82-31-717-5685    **SAMTEC ANZ** • Tel: 613 9580 0683