

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300130409

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change Receptacle, 4 Poles, Flange Mount, Male (Straight) to 16 AWG Leads, 0.305m (1.0') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

UL

E152210

General

Product Family

Industrial Receptacles

Series

130013

IP Rating

IP67

NEMA Rating

NEMA 6

Overview

Brad Mini-Change Connectors

Product Name

Mini-Change

Type

Single Ended (pigtail)

UPC

78678843917

Physical

Coupling Type

External Thread

Gender

Male

Keyway

Single

Length

0.305m

Material - Component

PVC

Mounting Thread Size

N/A

Orientation

Straight

Panel Mount

With Flange

Poles

4

Temperature Range - Operating

-20°C to +105°C

Wire Size AWG

16

Wire/Cable Type

UL 1015

Electrical

Current - Maximum per Contact

10.0A


Voltage - Maximum

600V

Material Info

Engineering Number

1R4G06A20A120



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130013 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION