

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


J

REV / 0720-0607-95

17JUL95

MLE

NB



AMP WIRE RANGE	UL E13288	LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED

1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16

2. WIRE INSUL DIA, 2.67-3.56 [.105-.140]

3. TONGUE MATERIAL THK: 0.79 ±0.05 [.031 ±.002]

-	-	-
1000	LOOSE PIECE	320773
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221° F]

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DWN
M ELLIS 16JUN95

CHK
C PRESNELL 16JUN95

APVD
N BIRCH 16JUN95

PRODUCT SPEC
UL 486A

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
TERMINAL, RING TONGUE, PIDG™,
WIRE SIZE, 22-16 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-320773

SCALE 4:1 SHEET 1 OF 1 REV J

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111


FOR ORDER ENTRY

1-800-526-5142

VOLTAGE RATING:
300 V MAX

CIRCULAR MIL AREA:
0.26mm² - 1.65mm² [509-3260]

DIMENSIONS:
mm [in]



MATERIAL
BODY, SLV, COPPER PER ASTM-B-152
INSUL, NYLON, COLOR, RED

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-

FINISH
BODY & SLV, TIN PLATE
PER MIL-T-10727