


[Request more info](#)

Part Number : 5510001902F



5510001902F



This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	551
Configuration	3 mm Lens
Description	3MM CBI 30 DEG ANGLE R/G
Package Options	Bulk Packaging
Lamp Type	Single Housing
Lens Style	Untinted, Diffused
Viewing Angle	60
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25°)

Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics

Color	Green	Red
Peak Wave Length	565	660
Luminous Intensity Min	1.1	3.7
Luminous Intensity Typical	3.7	12.6
Forward Voltage Typical	2.1	1.8
Forward Voltage Max	2.8	2.4
Test Current mA	20mA	