

SMT Power Inductors

Special Features

- Very high current capacity
- High reliability
- Low DCR
- Ferrite bobbin core
- Compact size
- Test frequency 100 KHz
- Operating temperature -40 to +85 °C
- Tape & reel packaged 500/reel

Typical Applications

- High current, low voltage converters
- High-speed computers
- Video game machines
- Output chokes
- EMI filters


Notes

- * Saturation current to cause 10 % inductance drop
- ** Rms current to cause 40 °C temperature rise

† RoHS Directive 2002/95/EC Jan 27 2003
including Annex.

PM3316H Series				
Part Number	L (μH) ±20 %	DCR (Ω) Max.	I, sat.* (A)	I, rms** (A)
PM3316H-R33M-RC	0.33	0.002	20	16
PM3316H-R68M-RC	0.68	0.005	13	12
PM3316H-1R0M-RC	1.0 0.	006	11	10
PM3316H-1R5M-RC	1.5 0.	008	9	9
PM3316H-2R2M-RC	2.2 0.	011	7.8	7.4
PM3316H-2R7M-RC	2.7	0.012	7	6.6
PM3316H-3R3M-RC	3.3	0.014	6.4	5.9
PM3316H-4R7M-RC	4.7	0.018	5.4	4.8

"-RC" suffix indicates RoHS compliance.



OBsolete

BOURNS®

Tel. (877) 426-8767 • Fax (951) 781-5006

www.bourns.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[PM3316H-R68M-RC](#) [PM3316H-3R3M-RC](#) [PM3316H-1R0M-RC](#) [PM3316H-2R2M-RC](#) [PM3316H-R33M-RC](#)
[PM3316H-1R5M-RC](#) [PM3316H-4R7M-RC](#) [PM3316H-2R7M-RC](#)