

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301090026](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Pro-Yellow Nylon 150W Incandescent Hand Lamp with Side Outlet and Switch, Grips Molded, Cord Type 16/3 SJTW, Cord Length 7.62m (25.0'), Easy Access Metal Guard

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E59049
General	
Product Family	Portable Lighting
Series	130109
NEMA Configuration	NEMA 5-15
Outlet	Side
Overview	Hand Lamps
Product Name	Pro-Yellow
Type	Hand Lamps
UPC	78678850115
Physical	
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Commercial
Guard Included	Yes
Guard Type	Steel
Height	N/A
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	1080.457/g
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	16/3 SJTW
Lamp Type	A21
Lamp Wattage - Maximum	150W
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	WT6C-25



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130109](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION