

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010112023

Status:


Active

Overview:

KK®

Description:

2.54mm (.100") Pitch KK® Crimp Terminal Housing, High Pressure, 2 Circuits



Documents:

3D Model

Drawing (PDF)

Product Specification PS-7879 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	7880
Overview	KK®
Product Name	KK®
Physical	
Circuits (maximum)	2
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface (in)	0.100 In
Pitch - Mating Interface (mm)	2.54 mm
Stackable	No
Temperature Range - Operating	0°C to +75°C
Electrical	
CSA	LR19980
UL	E29179
Material Info	
Old Part Number	7880-2B
Reference - Drawing Numbers	
Product Specification	PS-7879
Sales Drawing	SD-7880

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7880Series

Mates With

2.54mm (.100") Pitch KK® Crimp Terminal Housing, High Pressure, 2 Circuits

Use With

7879 KK® High Pressure Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION