




Telecommunication

ISDN U Transformer

Transformers

DT22-3601



DIMENSIONS IN mm

A	B	C	D	E	F	G
9.5 MAX.	3.7±0.5	20.0 MAX.	13.97±0.3	15.0 MAX.	2.54±0.12	

ELECTRICAL CHARACTERISTICS

URNS RATIO	1.8 ±1% @10KHz, 0.1V
INDUCTANCE	PRI: 14.5 mH ±10% @40KHz, 1V PRI: 12.5 mH Min. @40KHz, 1V Idc: 40mA
LEAKAGE INDUCTANCE	30 uH Max. @100KHz, 0.1V
D.C. RESISTANCE	PRI: 12.5 Ω Max. SEC: 5.45 Ω Max.
INTERWINDING CAPACITANCE	50 pF Max. @100KHz, 0.1V
INSERTION LOSS	1.0 dB Max. @10KHz 1.0 dB Max. @100KHz
DIELECTRIC STRENGTH	2500 VAC, 2 SEC @PRI TO SEC 500 VAC, 2 SEC @WDG TO CORE

DELTA ELECTRONICS, INC.

(TAOYUAN PLANT CPBG) 31-1, SHIEN PAN ROAD, KUEI SAN INDUSTRIAL ZONE, TAOYUAN SHIEN, TAIWAN, R.O.C.

TEL: 886-3-3626301 FAX: 886-3-3618901

<http://www.deltaww.com>