

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 19215-0045
Status: Active
Overview: Splices
Description: VersaKrimp™ Butt Splice for 4 AWG Wire

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Splices
Series 19215
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Splices
Product Name Butt, VersaKrimp™
UPC 800755062656

Physical

Barrel Type Closed - Brazed
Insulation None
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 14.092/g
Packaging Type Bag
Temperature Range - Operating 149°C
Wire Size AWG 4
Wire Size mm² 16.80 - 26.60

Electrical

Voltage - Maximum 600V

Material Info

Old Part Number F-364

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
Sales Drawing CD31003



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19215Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool	0640013900
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	0192940008
Manual Putt Pump Hydraulic System, Die set required	0192860117
Square "DIN" style dies for 4 AWG	0640037870
Die Set (large) for the HHLS Hydraulic Crimper	0192900007

This document was generated on 12/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION