



Mounted Points



- Pink abrasive mounted points
- Ideal for deburring, smoothing and general finishing applications
- The maximum recommended speeds given below are based on a maximum overhang of 133mm



Shape	Shank Ø	Size x Length	Max. Operating Speed rpm	Order Code	Shape	Shank Ø	Size x Length	Max. Operating Speed rpm	Order Code
A3	6	25 x 70	16100	700-9288	B135	3	6 x 13	60000	700-9409
A4	6	32 x 32	29840	700-9290	W144	3	3 x 6	105000	700-9410
A5	6	19 x 28	45000	700-9306	W160	3	6 x 6	81370	700-9422
A11	6	22 x 50	19860	700-9318	W162	3	6 x 10	68400	700-9434
A12	6	18 x 32	48000	700-9320	W163	3	6 x 13	60000	700-9446
A24	6	6 x 19	76500	700-9331	W176	3	10 x 13	45370	700-9458
A25	6	25 x 25	35620	700-9343	W205	6	19 x 25	34500	700-9471
B52	3	10 x 19	43370	700-9379	W220	6	25 x 25	25500	700-9483
B81	3	19 x 5	47750	700-9380	W227	6	32 x 13	29840	700-9495
B97	3	3 x 10	105000	700-9392					

225154

		Price Each
Shape	Order Code	
A3	700-9288	
A4	700-9290	
A5	700-9306	
A11	700-9318	
A12	700-9320	
A24	700-9331	
A25	700-9343	
B52	700-9379	
B81	700-9380	
B97	700-9392	
B135	700-9409	
W144	700-9410	
W160	700-9422	
W162	700-9434	
W163	700-9446	
W176	700-9458	
W205	700-9471	
W220	700-9483	
W227	700-9495	