



main menue



- home
- test & measurement
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
 - 2 mm system
 - 2 mm safety system
 - 4 mm system
 - 4 mm safety system
- sets
- miscellaneous
- company
 - portrait
 - corporate association
 - location maps
 - fairs and exhibitions
 - jobs
 - imprint
 - terms and conditions

Home > sockets > sockets > SEB 2620 F6,3

SEB 2620 F6,3

datasheet for SEB 2620 F6,3
article number: 972356101



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:		order number: 972 356-101	
description:		Safety built-in socket, 4 mm diameter, contact-protected, with 6.3 x 0.8 tab connector complying with DIN 46 244, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Installation hole: 12.2 mm diameter, Tightening torque: 50 Ncm, Accessory: assembly tool MW SEB	
typ:		SEB 2620 F6,3 rot/red	
system:		4mm safety system	
order number:		972 356-101	
color			
other color versions:			
technical data			
measurement category acc. to IEC 61010:		CAT III	
type of contact:		4 mm socket (unsprung)	
type of termination:		flat connector 6.3 x 0.8 mm	
rated voltage:		AC/DC 1000 V	
rated current:		32 A	
Please consider derating curve!			
contact resistance:		5 mOhm	
mounting:		screw	
material			
contact material:		brass	
contact surface material:		gold	
housing material:		PA	
connecting nut material:		brass nickel - plated	
environmental conditions:			
temperature range:		-40 °C to +80 °C	
inflammable class:			
housing (basic material):		UL 94 V - 2	
drawing			
			