




© COPYRIGHT 1964 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

1.52 [.060]




FLANGED IN
APPLICATOR



SECT A-A

SECT B-B



REVISIONS				
P	F	ZONE	LTR	DESCRIPTION
1			D	REDRAWN & REVISED A-3943
2			E	ADDED -3 TTI
3			F	OBSOLETE -3 PER A-5398
4			G	INSUL SUPP. LENGTH AF-0781
5			H	REVISED AF1994
		DATE	APPROVED	
		6-26-78	DD	SS
		9-5-79	PLT	RGF
		4-15-82	RS	64
		2-20-85	RS	64
		7/1/86	SS	RGF

1. CONTINUOUS STRIP ON REELS.
2. DIMENSIONS IN BRACKETS ARE IN INCHES.

△ SUFFIX LETTER MUST BE USED ONLY WHEN ORDERING APPLICATOR TOOLING.

METRIC

STUD SIZE		WIRE RANGE		INSULATION RANGE		FINISH		MATERIAL		PART NO	
M 4		0.8 - 2.0 mm ²		2.54 - 3.56		TIN		0.46		60774-1A	
# 8		[18-14]		[100 - 140]		NONE		BRASS		60774-1	