

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200988035

Status:

Active

Overview:

PROFIBUS Solutions

Description:

PROFIBUS Straight D-Sub Connector to Dual D-Sub, 22 AWG, PUR Cable, 1.0m (3.28') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                        |
|-------------------------------|------------------------|
| General                       |                        |
| Product Family                | Industrial Cordsets    |
| Series                        | 120098                 |
| Connector End A               | D-Sub (9-pin)          |
| Connector End B               | Dual D-Sub (9-pin)     |
| IP Rating                     | IP40                   |
| Material - Contact            | N/A                    |
| Overview                      | PROFIBUS Solutions     |
| Product Name                  | PROFIBUS               |
| Protocol                      | N/A                    |
| Region                        | America, Asia, Europe  |
| Type                          | Double Ended           |
| UPC                           | 78172507409            |
| Physical                      |                        |
| Cable Diameter                | 8.00mm (.315")         |
| Cable Length                  | 1.0m (3.28')           |
| Color - Cable Jacket          | Purple                 |
| Coupling Style                | Threaded               |
| Gender                        | Male-Male              |
| Keyway                        | None                   |
| LED Indicator                 | No                     |
| Material - Cable Jacket       | PUR                    |
| Material - Connector Body     | N/A                    |
| Material - Coupling Nut       | Gray Anodized Aluminum |
| Material - Plating Mating     | N/A                    |
| Orientation                   | 90° to Straight        |
| Poles                         | 9                      |
| Temperature Range - Operating | 0°C to +60°C           |
| Wire Size AWG                 | 22                     |
| Wire/Cable Type               | Shielded-Twisted Pair  |
| Electrical                    |                        |
| Current - Maximum per Contact | 4.0A                   |
| Voltage - Maximum             | 250V AC/DC             |
| Material Info                 |                        |
| Engineering Number            | MM3G72PP4M010          |
| Reference - Drawing Numbers   |                        |
| Sales Drawing                 | SD-120102-003          |



Series image - Reference only

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Reviewed                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Reviewed |
| ELV                                                           | Not Reviewed |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

120098 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION