


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

COVER REMOVED FOR CLARITY


PAN-TY LOOP FOR
CABLE HOLD-DOWN
(4 PLACES)



BREAKOUT AREA
(3 PLACES)

POST FOR TAMPER
RESISTANT SCREW

MOUNTING HOLES
FOR #6 PAN HEAD
SCREW (2 PLACES)



PANDUIT P/N

WEIGHT

CBX4**-AY

1.07 LB/10 PCS
(485 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. ALSO INCLUDED WITH BOX:
 - 1 - BOX BASE
 - 1 - BOX COVER
 - 2 - PLT1.51-C PAN-TY
 - 2 - MOUNTING SCREW
 - 1 - MOUNTING SCREW (USED TO SECURE COVER TO BASE)
 - 1 - LABEL/LABEL COVER
 - 2 - STRIP OF 1.25" X .75" FOAM TAPE FOR MOUNTING
5. BREAKOUTS DESIGNED TO ACCEPT LD3/LDP3 OR LD5/LDP5 RACEWAY.
6. BASE MATERIAL THICKNESS: .090(.2.29).

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

DRAWING FILENAME		SIZE									
MO2479EO_DC121_00A.PRT		A									
MINI-COM 4 POSITION SURFACE MOUNT BOX CUSTOMER DRAWING											
	PANDUIT TM CORP. TINLEY PARK, ILL 60477	I.I. NUMBER N/A									
	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .03(.8) ANGLES ±	PRODUCT SPEC N/A									
DRAWN BY Jsp	MATERIAL: ABS	WORK INSTRUCTION N/A									
DATE 1-26-07		SCALE NONE									
REV I-26-07 Jsp	ECN - R CUST SUP OTH	PART NO. CBX4**-AY									
RELEASED TO PRODUCTION		DRAWING NO. 02479-121									
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	CHK'D		

R I-26-07 Jsp

02479-121

REV DATE BY CHK DESCRIPTION

ECN

-

R

CUST

SUP

OTH

CHK'D