

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0210390359

Status:

Active - Custom

Overview:

Description:

1.00mm (.039") Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 20 Circuits, 0.076m (3.00") Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Cable

Series

21039

Comments

Contacts on the same side, Type A

Geographic Area

Americas

Overview

Premo-Flex™

Product Name

Premo-Flex™FFC Jumper

Physical

Cable Length

0.076m (3.00")

Circuits (Loaded)

20

Packaging Type

Bag

Pitch - Term. Interface (in)

0.039 In

Pitch - Term. Interface (mm)

1.00 mm

Temperature Range - Operating

-40°C to +80°C

Wire Size AWG

N/A

Wire/Cable Type

Flat Flex Cable

Electrical

Current - Maximum

1.3A

Voltage - Maximum

30V

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-21039-001



Series image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Halogen-Free Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Duration at Max. 30
Process Temperature (seconds)
Max. Cycles at Max. 1
Process Temperature
Process Temperature 250 max. C

Search Parts in this Series

21039 Series

Use With

Any 1.00mm (.039") Pitch Molex FFC/FPC connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION