

## E-Z OFF™ CABLE TIES

### E-Z OFF™ Cable Ties

**E-Z Off™ Cable Ties Provide for a Strong, Secure Locking Device that is Easily Removed without the Need of a Cutting Device. Comes in 6" and 8" with a Tensile Strength of 40. Use for Securing Shipping Containers, Attaching Sports Netting, Tag Attaching, Temporary Job Site Cabling, Agricultural Uses, Tier 1 & 2 Automotive Suppliers, Tenting, or Anywhere a Tie is Used as a Temporary Securing Device.**

To remove an E-Z Off™ tie, a user **simply pulls down on the tear-off arm** located on the right side of the head of the tie.

Since E-Z Off™ cable ties can be removed by hand, without a cutting device, the safety of your employees is enhanced and bundled material is undamaged. No more searching for a tool to remove the tie. E-Z Off™ cable ties allow **1 time use only**. Once removed, the tie cannot be re-attached or re-used.

| Retail Part No. | Length | Tensile Strength Min. | Color   | Pieces Per Bag | Maximum Bundle |
|-----------------|--------|-----------------------|---------|----------------|----------------|
| 34-490-C        | 6"     | 40 lbs./178 Newtons   | Natural | 100            | 1.5"           |
| 34-491-C        | 6"     | 40 lbs./178 Newtons   | Red     | 100            | 1.5"           |
| 34-492-C        | 6"     | 40 lbs./178 Newtons   | Blue    | 100            | 1.5"           |
| 34-493-C        | 6"     | 40 lbs./178 Newtons   | Green   | 100            | 1.5"           |
| 34-494-C        | 6"     | 40 lbs./178 Newtons   | Orange  | 100            | 1.5"           |
| 34-495-C        | 6"     | 40 lbs./178 Newtons   | Yellow  | 100            | 1.5"           |
| 34-496-C        | 6"     | 40 lbs./178 Newtons   | Purple  | 100            | 1.5"           |
| 34-497-C        | 6"     | 40 lbs./178 Newtons   | Black   | 100            | 1.5"           |
| 34-500-C        | 8"     | 40 lbs./178 Newtons   | Natural | 100            | 2.0"           |
| 34-501-C        | 8"     | 40 lbs./178 Newtons   | Red     | 100            | 2.0"           |
| 34-502-C        | 8"     | 40 lbs./178 Newtons   | Blue    | 100            | 2.0"           |
| 34-503-C        | 8"     | 40 lbs./178 Newtons   | Green   | 100            | 2.0"           |
| 34-504-C        | 8"     | 40 lbs./178 Newtons   | Orange  | 100            | 2.0"           |
| 34-505-C        | 8"     | 40 lbs./178 Newtons   | Yellow  | 100            | 2.0"           |
| 34-506-C        | 8"     | 40 lbs./178 Newtons   | Purple  | 100            | 2.0"           |
| 34-507-C        | 8"     | 40 lbs./178 Newtons   | Black   | 100            | 2.0"           |



**NOTE:** 40 lb tensile strength is 0.135" (3.43 mm) in width.



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6

| Retail Part No. | Bulk Part No. | Figure No. | Description            | Length | Holding Diameter | Tensile Strength (Pounds) | Color   |
|-----------------|---------------|------------|------------------------|--------|------------------|---------------------------|---------|
| 34-439-C        |               | 4          | Self Locking Cable Tie | 3-1/4" | 5/8"             | 18 lbs./80 Newtons        | Natural |
| 65032-C         |               | 1          | Self Locking Cable Tie | 4"     | 13/16"           | 18 lbs./80 Newtons        | Black   |
| 34-451-C        |               | 4          | Self Locking Cable Tie | 4"     | 13/16"           | 18 lbs./80 Newtons        | Natural |
| 34-452-C        |               | 2          | Self Locking Cable Tie | 6"     | 1-3/8"           | 30 lbs./133 Newtons       | Black   |
| 34-454-C        |               | 3          | Self Locking Cable Tie | 8"     | 2"               | 40 lbs./178 Newtons       | Black   |
| 65004-C         |               | 4          | Self Locking Cable Tie | 8"     | 2"               | 75 lbs./333 Newtons       | Natural |
| 34-458-C        |               | 5          | Cable Tie UV           | 11"    | 3"               | 60 lbs./267 Newtons       | Black   |
| 65036-C         |               | 5          | Self Locking Cable Tie | 15"    | 4"               | 120 lbs./534 Newtons      | Black   |

**NOTE:** 18 lb tensile strength is 0.097" (2.46 mm) in width.

30 lb tensile strength is 0.128" (3.25 mm) in width.

40 lb tensile strength is 0.135" (3.43 mm) in width.

50 lb tensile strength is 0.174" (4.42 mm) in width.

60 lb tensile strength is 0.167" (4.24 mm) in width.

120 lb tensile strength is special order only.

**For tie mounts, see wire section, page 427.**