



REV.	DATE	ECR NO.	DESCRIPTION
NC	05/12/09	XXXXXX	INITIAL RELEASE



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 ± 0.007" .315 - 1.180 ± 0.015" 1.180 - 4.724 ± 0.020" DO NOT SCALE DRAWING					APPROVALS		DATE		Amphenol Connex TNC REVERSE POLARITY PANEL JACK PART NO. 122248RP			
					DRAWN M.ZHANG		05/12/09					
					CHECKED							
					ISSUED							
					SHEET 1 OF 1							
QAD FILE C:/CONNEX/122248RP.DWG					DWG. NO. 122248RP.DWG		REV. NC		SIZE A		SCALE NA	
4	CONTACT PIN	BRASS	GOLD	1								
3	INSULATOR	PTFE	NATURAL	1								
2	BODY	BRASS	NICKEL	1								
1	HOUSING	BRASS	NICKEL	1								
DESCRIPTION		MATERIAL		FINISH	QTY							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122248RP](#)