


REV.	DATE	ECR NO.	DESCRIPTION
NC	01/26/09	—	INITIAL RELEASE
A	02/04/09	100076	REVISE NOTE 2, ADD LENGTH TABLE, REVISE B.O.M.



LENGTH TABLE	
PART NUMBER	LENGTH (IN.)
135110-03-06.00	6.00
135110-03-12.00	12.00
135110-03-24.00	24.00
135110-03-36.00	36.00

NOTE:

1. PERFORM CONTINUITY AND HI-POT TESTING.
2. PACKAGED INDIVIDUALLY IN HEAT SEALED POLY BAG.

4	009-954-341	HEAT SHRINK TUBING, BLACK, 3/16" DIAMETER	A/R FT
3	009-881-206	COAXIAL CABLE, RG316/U DOUBLE BRAID CABLE	A/R FT
2	132176	SMA BULKHEAD JACK, GOLD	1
1	132178	SMA STRAIGHT PLUG, GOLD	1
	PN	DESCRIPTION	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.40mm
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = ± 0.007"
.315 - 1.180 = ± 0.015"
1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS		DATE
DRAWN	G.R.S.	02/04/09
CHECKED		
ISSUED		
SHEET	1 OF 1	
CAD FILE	C:/135/135110-03-XX.XX.DWG	

Amphenol Connex

PART DESCRIPTION

SMA CABLE ASSEMBLY
STRAIGHT PLUG TO BULKHEAD JACK, RG316/U DB

PART NO.

135110-03-XX.XX

DWG. NO.

135110-03-XX.XX.DWG

REV. A

SIZE A

SCALE NA