


MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
12HR11-R1

12HR11-R1
RELEASER NO. PR-8664
REPLACES
DRAWING NUMBER
ISSUE
REVISIONS
A PR8664
W J M
13 JUN 80
B CO47277
J A P
8 JAN 81
C CO54204
G J W
15 NOV 83
D CO59096
T S K
14 NOV 86
E CO69306
S A V
15 MAR 90
F O-5285-A
DRAWN
W J M
13 JUN 80
CHECK C E B
18 JUNE 80
F O-5285-A
DRAWN
W J M
13 JUN 80
CHECK C E B
18 JUNE 80




CORROSION RESISTANT STEEL PLUNGER

3/4-20 UNEF THREAD TO WITHIN .150
OF SHOULDER

HEX NUT .938 ACROSS FLATS X .12
THICK (2) 6

INTERNAL TOOTH LOCKWASHER 1.06
DIA X .022 REF THICK 6

KEYING WASHER .98 DIA X .031 THICK,
TAB .110 WIDE 6



NOTES

- SWITCH SEALED PER MIL-S-8805 SWITCH CHAMBER. WATERTIGHT TEST NOT APPLICABLE
- ALL EXPOSED PARTS ARE CORROSION RESISTANT OR SUITABLY PLATED TO WITHSTAND CORROSION
- CIRCUIT DIAGRAM PERMANENTLY MARKED ON SWITCH HOUSING
- RECEPTACLE PIN IDENTIFICATION IS SHOWN ON CIRCUIT DIAGRAM
- SWITCH WILL OPERATE SATISFACTORILY IN TEMPERATURES FROM -85°F TO +400°F
- HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY
OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT
TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

RAW MATERIAL-COMMERCIAL STANDARD
MICRO SWITCH STANDARDS APPLY

DIMENSIONS ARE TO BE MET BEFORE
PROTECTIVE COATINGS ARE APPLIED

WEIGHT 6 OZ APPROX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell](#):

[12HR11-R1](#)