




NO.	ITEM	SPECIFICATION
1	Step Angle	$1.8^{\circ} \pm 5\%$
2	NO. of Phase	2
3	Rated Voltage	12V
4	Current Per Phase	0.4A
5	Resistance Per Phase	$30 \pm 10\% \Omega$
6	Inductance Per Phase	$32 \pm 20\% \text{mH}$
7	Holding Torque	2.1Kg-cm
8	Insulation Class	Class B
9	Insulation Resistance	100Mohm (500V DC)
10	Rotor Inertia	38g.cm^2

Rev.	Revision	Date
01	Update	3/22/2011



DRAWN	Kevin	3/22/2011	UNIT: mm		
CHECKED	Sara	3/22/2011			
ENG APPR.					
MFG APPR.			Sinotech		
Q.A.					
39BYG401A			SIZE A4	P/N 237472	REV 01
			SCALE: 2:1	Weight(kg):	SHEET 1 OF 1