

AULT SPECIFICATIONS

5-10 VA Wall Plug Series

INPUT

Voltage	120 VAC
Line Frequency	60 Hz
Configuration	North American Wall Plug, No Ground

OUTPUT

<i>Model Number</i>	<i>Rated Output Volts AC</i>	<i>Output Current Amps</i>	<i>Max. VA</i>
T41-042250-A000G	4	2.25	9.0
T41-051800-A000G	5	1.80	9.0
T41-061500-A000G	6	1.50	9.0
T41-071300-A000G	7	1.30	9.1
T41-080720-A000G	8	0.72	5.7
T41-080900-A000G	8	0.90	7.2
T41-081100-A000G	8	1.10	8.8
T41-090540-A000G	9	0.54	4.8
T41-090900-A000G	9	0.90	8.1
T41-091000-A000G	9	1.00	9.0
T41-100900-A000G	10	0.90	9.0
T41-120630-A000G	12	0.63	7.5
T41-120750-A000G	12	0.75	9.0
T41-150600-A000G	15	0.60	9.0
T41-160565-A000G	16	0.57	9.0
T41-180450-A000G	18	0.45	8.1
T41-180500-A000G	18	0.50	9.0
T41-200450-A000G	20	0.45	9.0
T41-220410-A000G	22	0.41	9.0
T41-240375-A000G	24	0.38	9.0

ELECTRICAL

Topology	Step Down AC/AC Transformer
Dielectric Withstand	1500 VAC primary-secondary
Protection	Current, Thermal or Energy Limiting
EMI	Meets FCC Class B
CE	NA

SAFETY APPROVALS

UL1310, CSA22.2-223

ENVIRONMENTAL

Operating Temperature	0° to 40° C with no derating
Storage Temperature	-30° to +85° C
Relative Humidity	5% to 95% non-condensing
Altitude	0 - 10,000 feet
Cooling	Convectional non-vented case

MECHANICAL

Case and Dimensions	T41 - North American Wall Plug 67 L X 53 W X 41 H (mm) 2.6 L X 2.1 W X 1.6 H (in)
Case Material	Black 94V1 Polycarbonate
Weight	9.6 ounces, 275 grams, (excluding cord)
Cord and Connectors	6 ft., 2 Conductor, 22-24 AWG, Ault #3 Connector Other connectors are also available

WARRANTY

1 Year