





Bost.



21



26



30



35



36



37



44



51






53



55

Selecting your screwdriver



Better grip on screw head:
Sand-blasted tip.

High quality durable blade:
Blade in molybdenum chrome vanadium, nickel-plated, and chrome-plated.

Hex bolster*
Use a wrench for stubborn screws.
*on certain models.



Effective
Comfortable push zone, both rigid and slipping for proper rotation in the palm of your hand.

Comfortable and effective grip:
Ergonomic handle adapted to your hand.

Fast screwing zone:
Antislip for better effectiveness

Handy:
Marking of the tip size and length of the blade



Easy to store:
Hooking hole for easy storage

Easy identification
Each tip size is colour coded.





ELECTRICIANS EXPERT SCREWDRIVER FOR SLOTTED HEAD SCREWS

NF ISO 2380-1/ NF ISO 2380-2 / DIN 5263



A x L2 x B	1	*	0	L1	Ø mm	7 g
2,0 x 50 x 0,4	624000	5	5	149	20	16
2,5 x 50 x 0,4	624010	4	5	149	20	18
3,0 x 50 x 0,5	624020	3	5	149	20	20
3,5 x 75 x 0,6	624030	2	5	177	27	37
3,5 x 100 x 0,6	624040	1	5	202	27	39
4,0 x 100 x 0,8	624060	9	5	202	27	43
4,0 x 125 x 0,8	624070	8	5	227	27	47
4,0 x 150 x 0,8	624080	7	5	252	27	50
5,5 x 125 x 1,0	624100	2	5	230	32	80
5,5 x 150 x 1,0	624110	1	5	255	32	85
5,5 x 175 x 1,0	624120	0	5	280	32	90
6,5 x 150 x 1,2	624140	8	5	266	40	133
6,5 x 200 x 1,2	624150	7	5	316	40	146

- Tip colour code: red.
- Comfortable and effective, trimaterial ergonomic handle.
- Machined and chrome-plated round blade. Sand-blasted tip.



EXPERT BALL HANDLE SCREWDRIVER FOR SLOTTED HEAD SCREWS

NF ISO 2380-1/ NF ISO 2380-2 / DIN 5263



A x L2 x B	1	*	0	L1	Ø mm	7 g
4,0 x 25 x 0,8	624900	8	5	86	32	33
5,5 x 25 x 1,0	624910	7	5	86	32	39
6,5 x 25 x 1,2	624920	6	5	86	32	45

- Tip colour code: red.
- Comfortable and effective, ergonomic trimaterial handle.
- Machined and chrome-plated round-shaped blade. Sand-blasted tip



EXPERT MECHANICS SCREWDRIVER FOR SLOTTED-HEAD SCREWS

NF ISO 2380-1/ NF ISO 2380-2 / DIN 5263



A x L2 x B	1	*	0	L1	Ø mm	7 g
5,5 x 100 x 1,0	624200	9	5	205	32	69
5,5 x 125 x 1,0	624210	8	5	230	32	73
6,5 x 125 x 1,2	624220	7	5	241	40	117
6,5 x 150 x 1,2	624230	6	5	266	40	123
8,0 x 150 x 1,2	624250	4	5	266	40	143
8,0 x 175 x 1,6	624260	3	5	291	40	177
10 x 200 x 1,6	624280	1	1	316	40	219

- Tip colour code: red.
- Comfortable and effective, ergonomic tri-material handle.
- Forged and chrome-plated round-shaped blade. Sand-blasted tip.



MECHANICS EXPERT SCREWDRIVER FOR SLOTTED-HEAD SCREWS WITH NUT

NF ISO 2380-1/ NF ISO 2380-2 / DIN 5263



A x L2 x B	1	*	0	L1	Ø mm	7 g	2
6,5 x 125 x 1,2	624320	4	5	241	40	124	10
6,5 x 150 x 1,2	624330	3	5	266	40	130	10
8,0 x 150 x 1,2	624350	1	5	266	40	150	11
8,0 x 175 x 1,6	624360	0	5	291	40	184	12
10 x 200 x 1,6	624380	8	1	316	40	226	14
12 x 250 x 2,0	624390	7	1	366	40	289	14

- Tip colour code: red.
- Comfortable and effective, ergonomic trimaterial handle.
- Forged and chrome-plated round-shaped blade. Sand-blasted tip.
- Hex bolster.



* For a full EAN, add the following
before the code: 303254


Bost

Catalogue 2005



EXPERT SCREWDRIVER FOR PHILLIPS® SCREWS

NF ISO 8764-1/ NF ISO 8764-2 / DIN ISO 8764-1/ DIN ISO 8764-2



C	6	x L2	1	*	0	L1	Ø mm	7 g
PH 00	3	x 50	624420	1	5	149	20	20
PH 0	4	x 75	624430	0	5	177	27	44
PH 1	5	x 100	624440	9	5	205	32	69
PH 2	6	x 125	624450	8	5	230	32	88

- Tip colour code: yellow.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round blade. Sand-blasted tip.



EXPERT SCREWDRIVER FOR PHILLIPS® SCREW - WITH NUT

NF ISO 8764-1/ NF ISO 8764-2 / DIN ISO 8764-1/ DIN ISO 8764-2



C	6	x L2	1	*	0	L1	Ø mm	7 g	2
PH 2	6	x 125	624480	5	5	230	32	95	10
PH 3	8	x 150	624490	4	1	266	40	167	12
PH 4	10	x 200	624500	0	1	316	40	254	14

- Tip colour code: yellow.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round-shaped blade. Sand-blasted tip.
- Hex bolster.




EXPERT BALL SCREWDRIVER FOR PHILLIPS® SCREWS

NF ISO 8764-1/ NF ISO 8764-2 / DIN ISO 8764-1



C	6	x L2	1	*	0	L1	Ø mm	7 g
PH 1	5	x 25	624930	5	5	86	32	37
PH 2	6	x 25	624940	4	5	86	32	42

- Tip colour code: yellow.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round-shaped blade. Sand-blasted tip.



* For a full EAN, add the following
before the code: 303254

Bost

Catalogue 2005



EXPERT SCREWDRIVER FOR POZIDRIV® SCREWS



D	6	x L2	1	*	0	L1	Ø mm	7 g
PZ 0	4	x 75	624540	6	5	177	27	41
PZ 1	5	x 100	624550	5	5	205	32	69
PZ 2	6	x 125	624560	4	5	230	32	88

- Tip colour code: blue.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round blade. Sand-blasted tip.



EXPERT SCREWDRIVER FOR POZIDRIV® SCREWS - WITH NUT



D	6	x L2	1	*	0	L1	Ø mm	7 g	2
PZ 2	6	x 125	624600	7	5	230	32	95	10
PZ 3	8	x 150	624610	6	1	266	40	165	12
PZ 4	10	x 200	624620	5	1	316	40	254	14

- Tip colour code: blue.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round blade. Sand-blasted tip
- Hex bolster.



EXPERT BALL HANDLE SCREWDRIVER FOR POZIDRIV® SCREWS




D	6	x L2	1	*	0	L1	Ø mm	7 g
PZ 1	5	x 25	624950	3	5	86	32	37
PZ 2	6	x 25	624960	2	5	86	32	42

- Tip colour code: blue.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated ball handle. Sand-blasted tip.



EXPERT SCREWDRIVER FOR SQUARE PATTERN FASTENERS



G	6	x L2	1	*	0	L1	Ø mm	7 g
SQ 1	4	x 100	625000	4	1	202	27	44
SQ 2	5	x 125	625010	3	1	230	32	73
SQ 3	6	x 150	625020	2	1	266	40	123

- Tip colour code: purple.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round blade. Sand-blasted tip.



E	6 x L2	1	*	0	L1	Ø mm	7 g
T 6	2,5 x 50	624650	2	5	148	20	18
T 7	2,5 x 50	624660	1	5	148	20	18
T 8	2,5 x 50	624670	0	5	148	20	18
T 9	3 x 75	624680	9	5	173	20	19
T 10	3 x 75	624690	8	5	177	27	34
T 15	3,5 x 75	624700	4	5	177	27	37
T 20	4 x 100	624710	3	5	202	27	44
T 25	5 x 100	624720	2	5	205	32	71
T 27	5 x 100	624730	1	1	205	32	75
T 30	6 x 125	624740	0	5	241	40	118
T 40	7 x 125	624750	9	5	241	40	135

- Tip colour code: green.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round blade. Sand-blasted tip.




F	6 x L2	1	*	0	L1	Ø mm	7 g
TT 10	3 x 75	624800	1	1	177	27	34
TT 15	3,5 x 75	624810	0	1	177	27	37
TT 20	4 x 100	624820	9	1	202	27	44
TT 25	5 x 100	624830	8	1	205	32	71
TT 27	5,5 x 100	624840	7	1	205	32	75
TT 30	6 x 125	624850	6	1	241	40	118
TT 40	7 x 125	624860	5	1	241	40	135

- Tip colour code: green.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round handle. Sand-blasted tip.



6 x L2	1	*	0	L1	Ø mm	7 g
5 x 75	625040	0	5	180	32	62



- Tip colour code: blue.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round blade. Sharp tip.



CARDED SETS

	1	*	0	W	B	C	7 g
					3,5 x 75	PH 1	
X5	849390	4	1	B7	4,0 x 100	PH 2	345
					5,5 x 125		

5 Expert screwdrivers blister



SETS IN BOXES

	1	*	W	B j	B p	C	D	0	7 g
X6	849610	3	CC	3,5x75	-	PH 0	-	1	510
				4,0x100	-	PH 1	-		
				5,5x125	-	PH 2	-		
x7	849600	4	CC	2,5 x 50	6,5x150	PH 1	-	1	600
				3,5x75		PH 2			
				4,0x100					
				5,5x125					
x7	849770	4	CC	2,5x50	6,5x150	-	PZ 1	1	585
				3,5x75			PZ 2		
				4,0x100					
				5,5x125					
x7	849990	6	CC	3,5x75	6,5x150	PH 1	PZ 1	1	677
				5,5x125		PH 2	PZ 2		
x8	849950	0	CC	3,5x75	6,5x150	PH 0	-	1	845
				4,0x100	8,0x150	PH 1			
				5,5x125		PH 2			
x8	849970	8	CC	3,5x75	5,5x125	PH 1	PZ 1	1	700
				4,0x100	6,5x150	PH 2	PZ 2		

Sets in boxes

- Set supplied in a cardboard box.
- Handy: the packaging's thermoformed base is used for storing screwdrivers in your workbench drawer.





g INSULATED SCREWDRIVER FOR ELECTRICIANS SLOTTED HEAD SCREWS

NF EN 60900



A x L2 x B	1	*	0	L1	Ø mm	7 g
2,5 x 50 x 0,4	626000	3	5	149	20	18
3,5 x 75 x 0,6	626010	2	5	177	27	38
3,5 x 100 x 0,6	626020	1	5	202	27	40
4,0 x 100 x 0,8	626030	0	5	202	27	43
4,0 x 150 x 0,8	626040	9	5	252	27	48
5,5 x 150 x 1,0	626050	8	5	255	32	84
5,5 x 175 x 1,0	626060	7	5	280	32	89
6,5 x 150 x 1,2	626070	6	5	266	40	134
6,5 x 200 x 1,2	626080	5	5	316	40	148

Expert insulated electrician's screwdriver

g

- Tip colour code: red.
- Comfortable and effective, ergonomic trimaterial handle.
- Round shaped blade, burnished with orange PVC insulation.
- Hollow carved imprint (type B) to improve stress resistance.



g INSULATED SCREWDRIVER FOR PHILLIPS® SCREWS

NF EN 60900



C	6 x L2	1	*	0	L1	Ø mm	7 g
PH 00	3 x 50	626120	8	5	149	20	21
PH 0	4 x 75	626130	7	5	177	27	40
PH 1	5 x 100	626140	6	5	205	32	68
PH 2	6 x 125	626150	5	5	230	32	89

Insulated Expert Phillips® screwdriver


g

- Tip colour code: yellow.
- Comfortable and effective, ergonomic trimaterial handle.
- Round blade, burnished with orange PVC insulation.



g INSULATED SCREWDRIVER FOR POZIDRIV® SCREWS

NF EN 60900




D	6 x L2	1	*	0	L1	Ø mm	7 g
PZ 0	4 x 75	626200	7	5	177	27	40
PZ 1	5 x 100	626210	6	5	205	32	68
PZ 2	6 x 125	626220	5	5	230	32	89

Expert insulated screwdriver for Pozidriv® screws

g

- Tip colour code: blue.
- Comfortable and effective, ergonomic trimaterial handle.
- Round blade, burnished with orange PVC insulation.



* For a full EAN, add the following before the code: 303254

Bost

Catalogue 2005



	1	*	W	B	C	D	0	7 g
X6	849790	2	CC	2,5 x 50 3,5 x 75 4,0 x 100 5,5 x 150	PH 1 PH 2	-	1	525
X6	849660	8	CC	2,5 x 50 3,5 x 75 4,0 x 100 5,5 x 150	-	PZ 1 PZ 2	1	525

- Handy: the packaging's thermoformed base is used to store the screwdrivers in your workbench drawers.



In cardboard case
with protecting
crystal window.



MIXED SETS

1	*	W	0	7 g
849440	6	CC	1	775

Electricians box with 5 tools

- Set:
 - 2 1000V Expert screwdrivers - EN 60900: 3.5 x 75 - 5.5 x 150.
 - 1 100 to 500V tip tester with clip (684050).
 - 1 electricians diagonal cutter* PVC with protections (Ø 1.6 to 160kg/mm²) (117310).
 - 1 crimping pliers* (127010).
- Set supplied in a cardboard case.
- Handy: the packaging's thermoformed base is used to store the screwdrivers in your workbench drawer.

* The pliers contained in this case are not 1000V insulated.



In cardboard case
with protecting
crystal window.

* For a full EAN, add the following
before the code: 303254

Bost



Counter display: Expert screwdrivers

4		1	*	A				1000V		C				D		E		
				2,5x50	3,5x75	4,0x100	5,5x125			PH00	PH0	PH1	PH2	PZ1	PZ2	T10	T15	T20
				624010	624030	624060	624100	626020	624220	624250	624420	624430	624440	624450	624550	624690	624700	624710
570 x 380 mm	x 170	849050	7	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10

MIXED LINEAR DISPLAY: EXPERT AND PRIMO SCREWDRIVERS



EXPERT + PRIMO display

Expert																		Primo																
4		1	*	A		1000V		2	C		D		E		A		C	D	L															
				2,5x50	3,5x75	4,0x100	5,5x125	3,5x100	5,5x150	6,5x150	8,0x150	5,5x25	PH2	PH0	PH1	PH2	PZ1	PZ2	T10	T15	T20	T25	T30	2,5x50	4,0x100	6,5x175	8,0x150	PH1	PH2	PH1	PH2	PZ1	PZ2	6x75
				624010	624030	624060	624100	626020	626050	624230	624250	624910	624940	624430	624440	624450	624550	624560	624690	624700	624710	624720	624740	616500	616520	616550	616820	617120	617130	617210	617220	617400	6x75	
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
				1000 x 370 mm	x 290	849060	6	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10

Expert+PRIMO NUT display

Expert																		Primo														
4		1	*	A		1000V				2		C		2		D		2		A		C		D								
				2,5x50	3,0x50	3,5x100	4,0x150	5,5x100	6,5x125	8,0x150	10x200	12x250	PH0	PH1	PH2	PH3	PZ0	PZ1	PZ2	PZ3	4,0x100	5,5x100	6,5x150	8,0x150	PH0	PH1	PH2	PZ0	PZ1	PZ2		
				624010	624020	626020	626040	624200	624220	624350	624380	624390	624430	624440	624480	624490	624540	624550	624600	624610	624620	624630	616520	616800	616810	616820	617110	617120	617130	617200	617210	617220
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
				10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
				1000 x 370 mm	x 270	849070	5	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10

BAR SYSTEM LINEAR DISPLAY



ONLY
FOR BAR
SYSTEM
LINEARS



Expert display

4		1	*	A		2		2		C		2		D		2		E		L		A 1000V													
				2,5x50	3,5x75	4,0x100	5,5x125	6,5x150	8,0x175	10x200	PH00	PH0	PH1	PH2	PH2	PH1	PH2	PZ0	PZ1	PZ2	PZ2	T10	T15	T20	T25	T30	T40	5x75	2,5x50	3,5x75	4,0x100	5,5x125	6,5x150	8,0x175	10x200
1330 x 390 mm	x 389	849080	4	15	12	24	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
1000 x 390 mm	x 297	849090	3	15	12	12	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
1330 x 390 mm	x 391	849100	9	15	12	24	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10

WOODEN SHELVES LINEAR DISPLAY



Expert display

4		1	*	A 1000V						2		C	2	D		2	E	L										
				2.5x50	3.5x75	4.0x100	5.5x150	2.5x50	3.5x75	4.0x100	5.5x125	6.5x150	8.0x150	10x200	6.5x150	8.0x175	10x200	PH00	PH0	PH1	PH2	PH2	T10	T15	T20	T25	T30	T40
1330 x 370 mm	x 365	849010	1	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
1330 x 370 mm	x 365	849030	9	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
1000 x 370 mm	x 265	849040	8	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10

* For a full EAN, add the following
before the code: 303254

iBost

Catalogue 2005


PRIMO ELECTRICIANS SCREWDRIVER FOR SLOTTED HEAD SCREWS

NF - E 74352 / ISO 2380 - 1 / DIN 5263



A x L2 x B	1	*	0	L1	Ø mm	7 g
2,5 x 50 x 0,4	616500	1	5	130	19	15
3,5 x 75 x 0,6	616510	0	5	155	19	20
3,5 x 100 x 0,6	616560	5	5	180	19	25
4,0 x 100 x 0,8	616520	9	5	202	27	52
4,0 x 150 x 0,8	616530	8	5	252	27	57
5,5 x 150 x 1	616540	7	5	252	27	76
6,5 x 175 x 1,2	616550	6	5	290	33	146

- Ergonomic bicolor handle designed specifically to apply powerful tightening torques.
- Chrome vanadium blade, round and nickel-plated.



A x L2 x B	1	*	0	L1	Ø mm	7 g
2,5 x 50 x 0,4	616600	8	5	130	19	17
3,5 x 75 x 0,6	616610	7	5	155	19	23
4,0 x 100 x 0,8	616620	6	5	202	27	54
5,5 x 150 x 1,0	616630	5	5	252	27	78

- Ergonomic bicolor handle designed specifically to apply high torque tightening.
- Chrome vanadium blade, round and nickel-plated.
- PVC sleeve on blade.
- High comfort sleeve, not guaranteed for working on live components.



PRIMO ELECTRICIANS BALL SCREWDRIVER FOR SLOTTED HEAD SCREWS

NF - E 74352 / ISO 2380 - 1 / DIN 5263



A x L2 x B	1	*	0	L1	Ø mm	7 g
5,5 x 25 x 1	617300	6	5	75	33	39
6,5 x 25 x 1,2	617310	5	5	75	33	43

- Ergonomic bicolor handle designed specially for difficult access.
- Nickel-plated round blade.




* For a full EAN, add the following
before the code: 303254

Bost

Catalogue 2005

PRIMO MECHANICS SCREWDRIVER FOR SLOTTED HEAD SCREWS

NF - E 74352 / ISO 2380 - 1 / DIN 5263




A x L2 x B	1	*	0	L1	Ø mm	7 g
5,5 x 100 x 1	616800	2	5	202	27	66
5,5 x 125 x 1	616840	8	5	227	27	71
6,5 x 125 x 1,2	616850	7	5	240	33	71
6,5 x 100 x 1,2	616810	1	5	265	33	129
8,0 x 150 x 1,2	616820	0	5	265	33	146
8,0 x 175 x 1,6	616860	6	5	290	33	173
10 x 200 x 1,6	616830	9	1	325	37	242

- Ergonomic bicolor handle designed specially to apply high tightening torques.
- Chrome vanadium blade, round and nickel-plated.

PRIMO SCREWDRIVER FOR PHILLIPS® SCREWS

NF - E 74355 / ISO 8764 - 1 / DIN 5260



C	6 x L2	1	*	0	L1	Ø mm	7 g
PH 00	3 x 50	617100	2	5	130	19	25
PH 0	4 x 75	617110	1	5	155	19	31
PH 1	5 x 100	617120	0	5	202	27	62
PH 2	6 x 125	617130	9	5	240	33	123
PH 2	6 x 200	617170	5	5	315	33	105
PH 3	8 x 150	617140	8	1	275	37	195

- Ergonomic bicolor handle designed specially to apply high torque tightening.
- Chrome vanadium blade, round and nickel-plated.

PRIMO BALL SCREWDRIVER FOR PHILLIPS® SCREWS


NF - E 74355 / ISO 8764 - 1 / DIN 5260



C	6 x L2	1	*	0	L1	Ø mm	7 g
PH 1	5 x 25	617320	4	5	75	33	37
PH 2	6 x 25	617330	3	5	75	33	42

- Ergonomic bicolor handle designed specially to apply high tightening torques.
- Chrome vanadium blade, round and nickel-plated.



PRIMO SCREWDRIVER FOR POZIDRIV® SCREWS



D	6 x L2	1	*	0	L1	Ø mm	7 g
PZ 0	4 x 75	617200	9	5	155	19	31
PZ 1	5 x 100	617210	8	5	202	27	62
PZ 2	6 x 125	617220	7	5	240	33	123
PZ 3	8 x 150	617230	6	1	275	37	195

- Ergonomic bicolor handle designed specially to apply high tightening torques.
- Chrome vanadium blade, round and nickel-plated.

PRIMO BALL SCREWDRIVER FOR POZIDRIV® SCREWS




D	6 x L2	1	*	0	L1	Ø mm	7 g
PZ 1	5 x 25	617340	2	5	75	33	37
PZ 2	6 x 125	617350	1	5	75	33	42

- Ergonomic bicolor handle designed specially to apply high tightening torques.
- Chrome vanadium blade, round and nickel-plated.



PRIMO SCREWDRIVER N



E	6 x L2	1	*	0	L1	Ø mm	7 g
T 10	3 x 75	617000	5	5	155	19	26
T 15	3,5 x 75	617010	4	5	155	19	28
T 20	4 x 100	617020	3	5	202	27	52
T 25	5 x 100	617030	2	5	215	33	104
T 30	6 x 125	617040	1	1	240	33	123
T 40	7 x 125	617050	0	1	250	37	167

- Ergonomic bicolor handle designed specifically to apply high tightening torque.
- Chrome vanadium blade, round and nickel-plated.

PRIMO TIP



6 x L2	1	*	0	L1	Ø mm	7 g
6 x 75	617400	3	5	190	33	114

- Chrome vanadium blade, round and nickel-plated.

Blister of 5 PRIMO screwdrivers

	1	*	0	w	B	C	7 g
					3,5 x 75	PH 1	
X5	811400	7	1	B7	4,0 x 100	PH 2	335
					5,5 x 150		

**SETS IN CARDBOARD CASES****Assortments in cardboard case**

	1	*	w	B j	B p	C	D	0	7 g
X7	811410	6	CC	2,5x50	5,5x100	PH 0			
						PH 1	-	1	520
				4,0x100	6,5x150	PH 2			
X9	811420	5	CC	2,5x50	5,5x100	PH 0	PZ 1		
						PH 1		1	610
				4,0x100	6,5x150	PH 2	PZ 2		

	1	*	w	B j	B p	C		0	7 g
x8	811500	4	CC	2,5 x 50		PH 0	x		
				3,5x75		PH 1	+		
				5,5x150		PH 2		1	620
				6,5x175					
x10	811510	3	CC	2,0x35		PH 0			
				2,5x50	5,5x100	PH 1			
				3,5x75	6,5x125	PH 2	x	1	540
				5,5x25					




Linear display

- Display with 275 screwdrivers Ref. 819030
- Display with 350 screwdrivers Ref. 819040

[illegible]

Counter display

- Display with 160 screwdrivers Ref. 819060



PRIMO g ELECTRICIAN'S SLOTTED-HEAD SCREWDRIVER

NF EN 60900



A x L2 x B	1	*	0	L1	Ø mm	7 g
2,5 x 50 x 0,4	618000	4	5	130	19	18
3,5 x 100 x 0,6	618020	2	5	180	19	30
4,0 x 100 x 0,8	618030	1	5	202	27	57
5,5 x 150 x 1,0	618040	0	5	252	27	75
6,5 x 150 x 1,2	618050	9	5	265	33	98
8,0 x 175 x 1,2	618060	8	1	290	33	155

Primo insulated screwdriver g

- Carved imprint (type B) to improve stress resistance.
- Round blade, burnished with red PVC insulation.



PRIMO PHILLIPS® g INSULATED SCREWDRIVER

NF EN 60900



C	6 x L2	1	*	0	L1	Ø mm	7 g
PH 1	5 x 100	618110	0	5	202	27	68
PH 2	6 x 125	618120	9	5	240	33	127

Primo insulated screwdriver g

- Round blade, burnished with red PVC insulation.



POZIDRIV® g INSULATED PRIMO SCREWDRIVER


NF EN 60900



D	6 x L2	1	*	0	L1	Ø mm	7 g
PZ 1	5 x 100	618210	7	5	202	27	68
PZ 2	6 x 125	618220	6	5	240	33	127

Primo insulated screwdriver g

- Round blade, burnished with red PVC insulation.



g INSULATED SCREWDRIVERS IN CARDBOARD CASES

NF EN 60900

	1	*	W	B t	C	D	100 500 volts	0	7 g
x6	812000	8	CC	2,5 x 50 3,5x75 4,0x100 5,5x150	PH 1 PH 2	-	-	1	480
x6	812010	7	CC	2,5x50 3,5x75 4,0x100 5,5x150	-	PZ 1 PZ 2	-	1	500
x5	812020	6	CC	2,5x50 3,5x75 4,0x100 5,5x150	-	-	x	1	320



* For a full EAN, add the following before the code: 303254

Bost

Catalogue 2005

ELECTRICIANS WOODEN SCREWDRIVER FOR SLOTTED-HEAD SCREWS

NF E 74352/ ISO 2380 - 1/ DIN 5263



A x L2 x B	1	*	0	L1	Ø mm	7 g
4,0 x 100 x 0,8	600050	0	5	200	22	36
5,0 x 125 x 1,0	600070	8	5	225	22	46

- Handle in hard wood, matt varnish.
- Round, burnished, blade.

MECHANICS FLAT-HEAD WOODEN HANDLE SCREWDRIVER

NF E 74352/ ISO 2380 - 1/ DIN 5263



A x L2 x B	1	*	0	L1	Ø mm	7 g
5,5 x 100 x 1,0	606100	6	5	200	22	51
6,5 x 125 x 1,2	606200	3	5	225	22	67
8,0 x 150 x 1,2	606350	5	5	260	25	102
9,0 x 150 x 1,3	606450	2	5	270	28	146
10 x 200 x 1,6	606600	1	5	330	32	216

With pass-through blade

- Hard wood handle, matt varnish.
- Round pass-through burnished blade.

WOODEN SCREWDRIVER FOR PHILLIPS® SCREWS

NF E 74355 / ISO 8764 - 1 / DIN 5260



C	6 x L2	1	*	0	L1	Ø mm	7 g
PH 1	5 x 100	604050	6	5	200	22	42
PH 2	6 x 125	604100	8	5	225	25	69

- Hard wood handle, matt varnish.
- Round blade, burnished.

WOODEN SCREWDRIVER SETS

In plastic pouch

	1	*	w	B j	B p	C	D	0	7 g
x8 800270	0	-	4,0x100 5,0x125	5,5x100 6,5x125 8,0x150 10x200	PZ 1 PZ 2 +	-	-	1	745
x4 800280	9	-	-	5,5x100 6,5x125 8,0x150 10x200	-	-	-	1	445

In cardboard case

	1	*	w	B j	B p	C	D	0	7 g
x5 833610	2	CC	-	5,5x100 6,5x125 8,0x150	PZ 1 PZ 2	-	-	1	400



* For a full EAN, add the following
before the code: 303254

Bost

Catalogue 2005



3 x 65 mm tester with clip

- From 100 to 500 volt with clip.
- Transparent handle.
- Round blade, nickel-plated, with sleeve.

A x L2	1	*	0	L1	W	7 g
3 x 65	684000	7	5	138	-	16
3 x 65	684006	9	5	138	B3	30



4 x 115 mm tester without clip

- From 100 to 500 volt without clip.
- Transparent handle.
- Round blade, nickel-plated, with sleeve.

A x L2	1	*	0	L1	W	7 g
4 x 115	684100	4	5	195	-	36
4 x 115	684106	6	5	195	B4	59



SC 3 x 60 mm current tester clip screwdriver



- For battery 6 to 24 volts.
- With crocodile clamp and clip.
- Transparent handle, round blade, nickel-plated, and with sleeve.

A x L2	1	*	0	L1	W	7 g
3 x 60	684156	1	5	135	B4	47

MULTIPLE BLADE SCREWDRIVERS IN A POUCH

B	C	y	Ø 5	1	*	0	W	7 g
3,5	PH 1			674100	7	1	T2	120
5,0	PH 2							
3,5	PH 1	x	x	674050	5	1	T2	145
5,0	PH 2							
3,5	PH 1			674150	2	1	T2	105
5,0	PH 2							

- Handle in blue acetate.
- Tightening by springs.
- Round nickel-plated blades.
- Supplied in a pouch.



* For a full EAN, add the following before the code: 303254

Bost

Catalogue 2005

Brass handle

- Storage handle and brass chuck.
- Nickel-plated round blades.


B	C	1	*	0	L1	Ø mm	W	7 g
1,5								
2,0	PH 00	637300	0	5	94	7	B3	15
2,5								
1,5								
2,0	PH 00	637306	2	1	94	7	B3	15
2,5								



Acetate handle

- Storage handle in acetate and brass chuck.
- Nickel-plated round blades.

B	C	y	1	*	0	L1	Ø mm	W	7 g
3,5									
5,0	PH 1	X	637000	9	5	155	14	-	58
3,5									
5,0	PH 1	X	637006	1	1	155	14	B3	72
2,0									
3,0			637050	4	5	135	11	-	28
3,5									
2,0									
2,5	PH 00		637106	8	1	105	8	B3	26
5,0									
6,0	PH 1	X	637156	3	1	210	60	B3	170
7,0	PH 2								
+	2x35								



POINTS



Square point

- Handle in blue acetate.
- Chrome vanadium square blade, sand-blasted and chrome-plated.

6 x L2	1	*	0	L1	Ø mm	W	7 g
8 x 125	675050	4	5	245	31	-	130
8 x 125	675057	3	5	245	31	S3	130



Expert point

- Colour code: blue.
- Comfortable and effective, ergonomic trimaterial handle.
- Chrome-plated round handle. Sharp tip.

6 x L2	1	*	0	L1	Ø mm	7 g
5 x 75	625040	0	5	180	32	62



Primo point

- Chrome vanadium blade, round and nickel-plated.


6	x L2	1	*	0	L1	Ø	7 g
						mm	
6 x 75	617400	3	5	190	33	114	



Wooden point

- Round and burnished pass-through blade.
- Hard wood handle, matt varnish.

6	x L2	1	*	0	L1	Ø	7 g
						mm	
7 x 100	675250	8	5	220	28	110	



IMPACT SCREWDRIVER



1	*	0	7 g
888950	9	1	1100

- Chrome-plated.
- Supplied in a metallic case including:
 - 1 intermediate socket for bit size 5/16" (7.94 mm).
 - 3 bits for slotted-head screw size 8 - 10 - 12 mm.
 - 3 bits for PHILLIPS® PH2 - PH3 - PH4 screws.
 - 6 bits for hollow hex screws 4 - 5 - 6 - 7 - 8 - 10 mm.



B	C	1	*	0	L1	Ø mm	7 g
6	PH 2	635720	8	5	170	22	55

- Blue acetate handle.
- Supplied with a reversible blade with an imprint for a slotted head screw and an imprint for Phillips® screw.
- Nickel-plated blade.

SMALL SLOTTED-HEAD SCREWDRIVERS



A x L2 x B	1	*	0	L1	Ø mm	W	7 g
2,0 x 35 x 0,4	631550	5	5	75	12,5	-	6
2,0 x 40 x 0,4	630050	1	5	100	13	-	8
2,5 x 50 x 0,4	631600	7	5	110	clips	-	10


- Blue acetate handle.
- Round nickel-plated chrome vanadium blade.

ANGLED SCREWDRIVERS



A x B	C	1	*	0	L1	W	7 g
5,5 x 1,0		650056	7	1	95	B3	34
8,0 x 1,2		656056	1	1	125	B3	51
PH 1 - PH 2		654056	3	1	145	B3	51

- For difficult access and powerful tightening of slotted head and Phillips® screws.
- Round blade in special steel.
- Burnished presentation.



1	*	0	W	7 g
682816	6	1	S4	91

- Magnetizes and demagnetizes screwdrivers, clamps, and other steel tools.
- Body in high grade ABS plastic, shock resistant.
- Supplied in plastic case with user manual.



EXPERT REVERSIBLE BLADE HOLDER WITH RATCHET



10-blade ratchet handle case

- Presentaion in metal case

c	B	C	D	E	H	1	*	0	W	7 g
		R	Q	N	A B					
x 10	0,8 x 4,0			T10/T15	4 x 4	649160	5	1	B7	1240
	1,2 x 6,5	PH 1	PZ 1	T20/T25	5 x 5					
	1,0 x 5,5	PH 2	PZ 2	T30/T40	6 x 6					
	1,2 x 7,0									

EXPERT-PC SCREWDRIVER FOR SLOTTED-HEAD SCREWS

NF - E 74352 / ISO 2380 - 1 / DIN 5263




A x L2 x B	1	*	0	L1	W	7 g
1,0 x 40 x 0,2	649206	0	1	120	B2	19
1,5 x 40 x 0,25	649220	6	5	120	-	8
1,5 x 40 x 0,25	649226	8	1	120	B2	19
2,0 x 40 x 0,4	648000	5	5	120	-	9
2,0 x 40 x 0,4	648006	7	1	120	B2	20
2,5 x 40 x 0,4	648026	5	1	120	B2	21
3,0 x 40 x 0,5	648040	1	5	120	-	11
3,0 x 40 x 0,5	648046	3	1	120	B2	22

- Chrome vanadium nickel-plated steel blade.
- Cellulosis acetate handle.
- Swivel finger rest.

EXPERT-PC SCREWDRIVER FOR PHILLIPS® SCREWS

NF - E 74355 / ISO 8764 - 1 / DIN 5260



C	A x L2	1	*	0	L1	W	7 g
PH 000	2,0 x 40	648060	9	5	120	-	11
PH 000	2,0 x 40	648066	1	1	120	B2	22
PH 00	2,5 x 40	648070	8	5	120	-	11
PH 00	2,5 x 40	648076	0	1	120	B2	22
PH 0	3,0 x 40	648080	7	5	120	-	13
PH 0	3,0 x 40	648086	9	1	120	B2	24

- Chrome vanadium nickel-plated steel blade.
- Cellulosis acetate handle.
- Swivel finger rest.

EXPERT-PC SCREWDRIVER N



E	A x L2	1	*	0	L1	W	7 g
T6	2,0 x 40	648156	9	1	120	B2	21
T7	2,5 x 40	648166	8	1	120	B2	22
T8	2,5 x 40	648176	7	1	120	B2	22
T9	3,0 x 40	648186	6	1	120	B2	22

- Chrome vanadium nickel-plated steel blade.
- Cellulosis acetate handle.
- Swivel finger rest.


MULTIBLADE EXPERT-PC SCREWDRIVER



- Chrome vanadium nickel-plated steel blade.
- Cellulosis acetate handle.
- Swivel finger rest.



Composition	1	*	0	L1	W	7 g
1 - 1,2 - 1,5 - 1,8	648386	0	1	120	B2	28
1,5 - 1,8 - 2 - 2,5	648396	9	1	120	B2	28
PH 000 - PH 00 - 2 - 2,5	648406	5	1	120	B2	28



* For a full EAN, add the following before the code: 303254

Bost

Catalogue 2005

Fixed blades

- Fixed blades and plastic case.

		1	*	0	W	B	C	E	7 g
X4	648910	7	1	CP2				T6 T7 T8 T9	125
X6	648900	8	1	CP2	2,0 x 40 2,5 x 40 3,0 x 40 1,0 x 40 1,2 x 40 1,5 x 40 1,8 x 40 2,0 x 40 2,5 x 40	PH 000 PH 00 PH 0			150
x6	649300	5	1	CP2	1,0 x 40 1,2 x 40 1,5 x 40 1,8 x 40 2,0 x 40 2,5 x 40				155
x6	649310	4	1	CP2	1,0 x 40 1,2 x 40 1,5 x 40 1,8 x 40	PH 000 PH 00			150



Multiple blades

- Multiple blades and plastic case.

B	C	1	*	0	W	7 g
1,0 x 40 1,2 x 40 1,5 x 40 1,8 x 40 2,0 x 40 2,5 x 40	PH 000 PH 00	648950	3	1	CP2	70



High precision screwdriver

- Professional models for clockwork, optics, electronics.
- Body in nickel-plated brass, colour ring.
- Rotating finger rest.

	1	*	0	W	B	C	7 g
x5	888110	7	1	-	0,8 1,0 1,2 1,6 2,0		45
x5	888117	6	1	S5	0,8 1,0 1,2 1,6 2,0		55
x5	888120	6	1	-	1,0 1,2 1,6	PH 000 PH 00	60



25MM BITS FOR SLOTTED HEAD SCREWS

NF-E 74360 - ISO 1173 - DIN 3126



- Hex drive 1/4": 6.35 mm.
- High performance steel.
- Surface hardness 58/60 HRC.
- Manual use or with a runner.

AxL2	B	1	*	0	W	7 g
4,0 x 25		682860	9	5	-	5
4,5 x 25	0,6	683200	2	10	-	5
5,5 x 25	0,8	683250	7	10	-	5
6,5 x 25	1,2	683300	9	10	-	5
8,0 x 25	1,2	683260	6	10	-	5




25MM BITS FOR PHILLIPS® SCREWS

NF-E 74360 - ISO 1173 - DIN 3126



C	L	1	*	0	W	7 g
PH 0	25	683320	7	10	-	5
PH 1	25	683350	4	10	-	5
PH 2	25	683402	0	50	-	5
PH 3	25	683450	1	10	-	5




25MM BITS FOR POZIDRIV® SCREWS

NF-E 74360 - ISO 1173 - DIN 3126



D	L	1	*	0	W	7 g
PZ 1	25	683502	7	50	-	5
PZ 2	25	683552	2	50	-	5
PZ 2	25	683556	0	1	B1	14
PZ 3	25	683602	4	50	-	5



* For a full EAN, add the following before the code: 303254

Bost

Catalogue 2005

25MM BITS FOR N SCREWS



- 1/4" hex drive: 6.35 mm.
- High performance steel.
- Surface hardness 58/60 HRC.
- Manual use or with a runner.



E	L	1	*	0	W	7 g
T10	25	683660	4	10	-	5
T15	25	683670	3	10	-	5
T20	25	683680	2	10	-	5
T25	25	683690	1	10	-	5
T30	25	683700	7	10	-	7
T40	25	683720	5	10	-	7


25MM BITS FOR TAMPER N SCREWS



F	L	1	*	0	W	7 g
TT20	25	687820	8	5	-	5

25 MM BITS FOR HOLLOW HEX SCREWS

H	L	1	*	0	W	7 g
2	25	682910	1	5	-	5
3	25	682900	2	10	-	5
4	25	682920	0	10	-	5
5	25	682940	8	10	-	5
6	25	682960	6	10	-	5
8	25	682880	7	5	-	5



* For a full EAN, add the following before the code: 303254

Bost

Catalogue 2005

50 MM BITS FOR PHILLIPS® SCREWS



- 1/4" hex drive: 6.35 mm.
- High performance steel.
- Surface hardness 58/60 HRC.
- Manual use or with runner.

C	L	1	*	0	W	7 g
PH 1	50	683140	1	10	-	10
PH 2	50	683150	0	10	-	10

50 MM BITS FOR POZIDRIV® SCREWS



- 1/4" hex drive: 6.35 mm.
- High performance steel.
- Surface hardness 58/60 HRC.
- Manual use or with runner.

D	L	1	*	0	W	7 g
PZ 1	50	683170	8	10	-	10
PZ 2	50	683180	7	10	-	10


MAGNETIC SOCKETS



For hex head screws

- 1/4" hex drive = 6.35 mm.
- For cladding work.
- For self-drilling screws.
- Steel grey presentation.

H	L	1	*	0	W	7 g
7	65	684610	8	5	-	30
8	65	684620	7	5	-	35
8	65	684626	9	1	B1	44
10	65	684630	6	5	-	40
10	65	684636	8	1	B1	40
13	65	684640	5	5	-	50



* For a full EAN, add the following before the code: 303254

Set of 11 bits

- 25 mm bits and magnetic adapter.
- Presentation in storage pouch.

B	C	D	E	1	*	0	W	7 g
4,0 5,5 6,5	PH 1 PH 2	PZ 1 PZ 2	T10 - T15 T20 - T25	687736	2	1	B6	105



Set of bits in round dispensing box

- 25 mm bits and magnetic adapter.
- Presentation in storage box Ø 77 x 17.5 mm.

B	C	D	E	1	*	0	W	7 g
4,5 6	PH 1 PH 2	PZ 1 PZ 2	-	684700	6	1	-	75
4,5 6	PH 1 PH 2	PZ 1 PZ 2	-	684706	8	1	B6	90



Set of bits in barrel box with screwdriver function

- 25 mm bits and magnetic adapter.
- Dimensions: Ø 41 x 78 mm.

Qté	B	C	D	1	*	0	W	7 g
x6	4,5 6	PH 1 PH 2	PZ 1 PZ 2	684740	2	1	-	125
x6	4,5 6	PH 1 PH 2	PZ 1 PZ 2	684746	4	1	B6	-



L1	1	*	0	W	7 g
110	683986	5	1	B6	75



- For bits 25 mm long.
- 1/4" hex drive = 6.35 mm with retaining ball.
- Presentation chrome-plated body, synthetic comfort sleeve, length 110 mm.
- Supplied without bits.

REVERSIBLE RATCHET

L1	1	*	0	W	7 g
110	690580	5	5	-	55



- For bits length 25 mm or 1/4" socket.
- 1/4" hex drive = 6.35 mm.
- Increment 30°.
- Knurled head for fast approach.
- Presentation chrome-plated body, length = 110mm.
- Supplied without bits or sockets.

REVERSIBLE RATCHET + 7 BITS

B	C	D	1	*	0	W	7 g
4,5	PH 1	PZ 1	690596	6	1	B6	150
	PH 2						
6	PH 3	PZ 2					



- For bits length 25 mm or 1/4" socket.
- 1/4" hex drive = 6.35 mm.
- Increment 30°.
- Knurled head for fast approach.
- Presentation chrome-plated body, length = 110mm.
- Composed of 7 bits, including 1 fitted and 6 in magazine.

L1	1	*	0	W	7 g
60	683900	1	5	-	25
60	683906	3	5	B1	34
120	683990	2	5	-	55



Magnetic bit holder adapters

- For bits length 25 mm.



L1	1	*	0	W	7 g
50	683930	8	5	-	15

Bit holder adapter 50 mm

- Drive square 6.35 mm.
- Retaining ball for 1/4" sockets.

TURN 6



L1	1	*	0	W	7 g
250	639510	1	3	-	150


Empty bit holder screwdriver

- Transparent acetate handle.
- Handle has direct grip on the bit, preventing any loss of force during power tightening.
- Nickel-plated blade fitted with a chrome-plated magnetic adapter.
- High quality elastomere cap.



B	C	D	E	1	*	0	W	7 g
0,6 x 4,5	PH 1	PZ 1		639560	6	3	-	180
1,2 x 6,5	PH 2	PZ 2						
0,6 x 4,5	PH 1	PZ 1		639566	8	1	B5	209
1,2 x 6,5	PH 2	PZ 2						
		T10-T15						
		T20-T25		639570	5	3	-	180
		T30-T40						

Turn 6 with bits





L1	1	*	0	W	7 g
230	625070	7	1	-	107
230	625076	9	1	B4	121

Expert bit holder screwdriver

- Expert trimaterial ergonomic handle.
- length of the blade 125 mm
- Fitted with a magnetic adapter

Expert bit holder screwdriver

- Expert ergonomic trimaterial handle.
- length of the blade 125 mm.
- Fitted with a magnetic adapter.
- Supplied with 6 bits and a holder.


B	C	1	*	0	W	7 g
4,5	PH 1					
5,5	PH 2	639256	8	1	B7	134
6,5	PH 3					



Expert bit holder screwdriver case

- With magnetic adapter for runner and 17 bits


B	B	D	E	H	1	*	0	W	7 g
			T10						
4,0	PH 1	PZ 1	T15	3,0					
4,5	PH 2	PZ 2	T20	4,0	639240	7	1	CPB	455
6,5	PH 3	PZ 3	T25	5,0					
			T30						



STANDARD METRIC SERIES

NF-E 74 331 / ISO 2936 / DIN 911

6 mm	1	*	0	L x l	W	7 g
0,9	660026	7	5	38 x 12	B1	9,32
1,5	660040	3	10	45 x 14	-	0,88
1,5	660043	4	100	45 x 14	-	0,88
1,5	660046	5	5	45 x 14	B1	9,88
2	660060	1	10	50 x 16	-	2
2	660063	2	100	50 x 16	-	2
2	660066	3	5	50 x 16	B1	11
2,5	660080	9	10	56 x 18	-	3
2,5	660083	0	100	56 x 18	-	3
2,5	660086	1	5	56 x 18	B1	12
3	660100	4	10	63 x 20	-	5
3	660103	5	100	63 x 20	-	5
3	660106	6	5	63 x 20	B1	14
3,5	660120	2	10	66 x 22	-	7
3,5	660123	3	100	66 x 22	-	7
4	660140	0	10	70 x 25	-	10
4	660143	1	100	70 x 25	-	10
4	660146	2	5	70 x 25	B1	19
4,5	660160	8	10	75 x 26	-	14
4,5	660163	9	100	75 x 26	-	14
5	660180	6	10	80 x 28	-	18
5	660183	7	100	80 x 28	-	18
5	660186	8	5	80 x 28	B1	27
6	660200	1	10	90 x 32	-	30
6	660202	5	50	90 x 32	-	30
6	660206	3	5	90 x 32	B1	39
7	660220	9	10	95 x 34	-	43
7	660222	3	50	95 x 34	-	43
7	660226	1	5	95 x 34	B1	57
8	660240	7	10	100 x 36	-	60
8	660242	1	50	100 x 36	-	60
8	660246	9	5	100 x 36	B1	74
9	660260	5	10	105 x 38	-	79
9	660261	2	25	105 x 38	-	79
9	660266	7	5	105 x 38	B1	93



Metric hex keys

- Manufactured in chrome vanadium steel, torque resistance exceeding currently enforced standards.
- Edges micro-chamfered for enhanced maintaining of screw head.
- Burnished presentation.

6 mm	1	*	0	L x l	W	7 g
10	660280	3	10	112 x 40	-	104
10	660281	0	25	112 x 40	-	104
10	660286	5	5	112 x 40	B1	118
11	660300	8	5	118 x 42	-	143
11	660306	0	5	118 x 42	B1	146
12	660320	6	5	125 x 45	-	168
12	660321	3	25	125 x 45	-	168
12	660326	8	5	125 x 45	B1	182
13	660340	4	1	132 x 50	-	212
14	660360	2	1	140 x 56	-	264
15	660380	0	1	146 x 58	-	316
16	660400	5	1	152 x 60	-	377
17	660420	3	1	160 x 63	-	444
18	660440	1	1	170 x 66	-	529
19	660460	9	1	180 x 70	-	623

LONG METRIC SERIES

NF-E 74 331 / ISO 2936 / DIN 911

6 mm	1	*	0	L x l	W	7 g
1,5	662050	0	5	62 x 14	-	1
1,5	662053	1	100	62 x 14	-	1
2	662100	2	5	75 x 16	-	2
2	662103	3	100	75 x 16	-	2
2,5	662150	7	5	85 x 18	-	4
2,5	662153	8	100	85 x 18	-	4
3	662200	9	5	90 x 20	-	7
3	662203	0	100	90 x 20	-	7
4	662250	4	5	100 x 25	-	13
4	662253	5	100	100 x 25	-	13
5	662300	6	5	115 x 28	-	24
5	662303	7	100	115 x 28	-	24
6	662350	1	5	135 x 32	-	41
6	662352	5	50	135 x 32	-	41
7	662400	3	1	140 x 34	-	58
7	662402	7	50	140 x 34	-	58
8	662450	8	5	150 x 36	-	81
8	662452	2	50	150 x 36	-	81
9	662500	0	1	160 x 38	-	109
10	662550	6	5	170 x 40	-	142
10	662551	2	25	170 x 40	-	142
11	662600	7	1	180 x 42	-	181
12	662650	2	5	190 x 45	-	210
12	662651	9	25	190 x 45	-	210



Long metric keys

- Manufactured in chrome vanadium steel, torque resistance exceeding currently enforced standards.
- Edges micro-chamfered for enhanced maintaining of screw head.
- Burnished presentation.




SPHERICAL HEAD SERIES

6 mm	1	*	0	L x l	W	7 g
1,5	664020	1	5	62 x 14	-	1
2	664040	9	5	72 x 16	-	2
2,5	664060	7	5	85 x 18	-	4
3	664080	5	5	90 x 20	-	7
4	664100	0	5	100 x 25	-	13
5	664120	8	5	115 x 28	-	24
6	664140	6	5	135 x 32	-	36
7	664150	5	1	140 x 34	-	58
8	664160	4	1	150 x 36	-	80
10	664180	2	1	170 x 40	-	139



Spherical head hex keys

- Burnished presentation.



KEYS N

E	1	*	0	L x l	W	7 g
T6	681030	7	5	43 x 15	-	2
T6	681036	9	1	43 x 15	B1	11
T7	681040	6	5	47 x 15	-	2
T7	681046	8	1	47 x 15	B1	11
T8	681050	5	5	47 x 15	-	2
T8	681056	7	1	47 x 15	B1	11
T9	681060	4	5	47 x 15	-	3
T9	681066	6	1	47 x 15	B1	12
T10	681080	2	5	50 x 16	-	4
T10	681086	4	1	50 x 16	B1	13
T15	681100	7	5	54 x 18	-	5
T15	681106	9	1	54 x 18	B1	14
T20	681120	5	5	57 x 19	-	7
T20	681126	7	1	57 x 19	B1	16
T25	681140	3	5	60 x 20	-	9
T25	681146	5	1	60 x 20	B1	18
T27	681150	2	5	63 x 21	-	15
T30	681180	9	5	70 x 24	-	20
T30	681186	1	1	70 x 24	B1	29
T40	681200	4	5	76 x 26	-	29
T40	681206	6	1	76 x 26	B1	38
T45	681216	5	1	82 x 28,5	B3	49
T50	681220	2	5	94 x 31	-	46
T50	681226	4	1	94 x 31	B3	60





- Burnished presentation.

DRAIN-PLUG WRENCH

NF-E 74 331 / ISO 2936 / DIN 911

G	1	*	0	L x l	W	7 g
8	668107	5	1	170 x 55	S	109
10	668207	2	1	145 x 40	S	231



- Manufactured in chrome vanadium steel for torque resistance exceeding currently enforced standards.
- Edges microchamfered for enhanced maintaining of screw heads.
- Square key.
- Burnished presentation.

* For a full EAN, add the following before the code: 303254

Bosch

Catalogue 2005

SET ON RING

Set of metric hex wrenches

Qty	H	1	*	0	W	7 g
x8	1,5 - 2 - 2,5 - 3 4 - 5 - 6 - 8	866050	4	1	-	149
x8	1,5 - 2 - 2,5 - 3 4 - 5 - 6 - 8	866056	6	1	B9	183

Set of hex keys in inches

Qty	H	1	*	0	W	7 g
x8	5/64" - 3/32" 1/8" - 5/32" 3/16" - 7/32" 1/4" - 5/16"	866106	8	1	B9	209

Set of rings N

Qty	E	1	*	0	W	7 g
x8	T9 - T10 - T15 T20 - T25 - T27 T30 - T40	888930	1	1	-	115
x8	T9 - T10 - T15 T20 - T25 - T27 T30 - T40	888936	3	1	B9	149



SET ON PLASTIC HOLDER

Metric hex keys

- Reference 866450 is made of long keys

Qty	H	1	*	0	W	7 g
x9	1,5 - 2 - 2,5 - 3 4 - 5 - 6 - 8 - 10	866400	7	1	-	250
x9	1,5 - 2 - 2,5 - 3 4 - 5 - 6 - 8 - 10	866406	9	1	B9	384
x9	1,5 - 2 - 2,5 - 3 4 - 5 - 6 - 8 - 10	866450	2	1	-	350

Spherical head hex keys

Qty	H	1	*	0	W	7 g
x7	1,5 - 2 - 2,5 - 3 4 - 5 - 6	866440	3	1	-	125
x7	1,5 - 2 - 2,5 - 3 4 - 5 - 6	866446	5	1	B9	159
x9	1,5 - 2 - 2,5 - 3 4 - 5 - 6 - 8 - 10	866500	4	1	-	350
x 9	1,5 - 2 - 2,5 - 3 4 - 5 - 6 - 8 - 10	866506	6	1	B9	384

Holder of spherical head 9 keys in inches

Qty	H	1	*	0	W	7 g
x9	1/16" - 5/64" 3/32" - 1/8" 5/32" - 3/16" 7/32" - 1/4" - 3/8"	866470	0	1	-	350



Set on plastic holder N

Qty	E	1	*	0	W	7 g
x7	T10 - T15 T20 - T25 - T27 T30 - T40	888970	7	1	-	96
x7	T10 - T15 T20 - T25 - T27 T30 - T40	888976	9	1	-	130

Holder of 7 Tamper keys N

Qty	F	1	*	0	W	7 g
x7	TT10 - TT15 - TT20 TT25 - TT27 TT30 - TT40	889050	5	1	-	96



SETS - KEY CHAIN

Sets of hex chain

Qty	H	1	*	0	W	7 g
x7	1,5 - 2 - 2,5 3 - 4 - 5 - 6	866650	6	1	T1	75
x8	3 - 4 - 5 - 6 7 - 8 - 10 - 12	866600	1	1	T1	455
x10	2 - 2,5 - 3 4 - 5 - 6 - 7 8 - 9 - 10	866700	8	1	T2	370
x13	3 - 4 - 5 6 - 7 - 8 - 9 10 - 11 - 12 14 - 17 - 19	866750	3	1	T3	2020

Sets in chain N

Qty	E	1	*	0	W	7 g
x6	T10 - T15 - T20 T25 - T30 - T40	888920	2	1	-	85
x6	T10 - T15 - T20 T25 - T30 - T40	888927	1	1	S5	106



Metric combination

- Burnished keys and composite holder reinforced by a steel spacer ensuring its rigidity.
- Axis in steel independent from the screw and nut tightening system.
- Used to apply high torque tightening.
- Comfortable grip and keys stopped at 270°.
- Dimension marking and hooking hole.

Qty	H	1	*	0	W	7 g
x5	4 - 5 - 6 8 - 10	888610	2	1	-	255
x8	1,5 - 2 - 2,5 - 3 4 - 5 - 6 - 8	888620	1	1	-	200



Combination of 5 spherical head wrenches - metric

Qty	H	1	*	0	W	7 g
x5	4 - 5 - 6 8 - 10	888640	9	1	-	255



Combination of 7 wrenches N

Qty	E	1	*	0	W	7 g
x7	T10 - T15 T20 - T25 - T27 T30 - T40	888660	7	1	-	240



Combination of 7 Tamper wrenches N

Qty	F	1	*	0	W	7 g
x7	TT10 - TT15 - TT20 TT25 - TT27 TT30 - TT40	888670	6	1	-	240



H	1	*	L	A	B	C	O	W	7 g
2	647500	1	126	100	10	53	3	-	7
2,5	647510	0	126	100	10	53	3	-	9
3	647520	9	126	100	10	53	3	-	12
4	647530	8	183	150	11	66	3	-	58
5	647540	7	183	150	12	66	3	-	70
6	647550	6	240	200	12	82	3	-	112

Assortment with P handle

1	*	H	O	W	7 g
847520	7	2 - 2,5 - 3 4 - 5 - 6	1	CC	450

Assortment N

1	*	E	O	W	7 g
847540	5	T10 - T15 T20 - T25 T30 - T40	1	CC	490

1	*	L	A	C	O	7 g
647800	2	165	125	82	1	85

P handle

- Ergonomic handle in blue acetate.
- Long part of the wrench for easy access to confined locations and fast tightening.
- Angled part for power tightening.
- Burnished presentation.



EXPERT 1/4" bit holder handle

- Sand-blasted, chrome-plated blade.
- Magnetic adapter for 0.25 mm bit magnetic adapter.
- 6.35 mm = 1/4".

HANDLE-FITTED KEYS

H	1	*	6 mm	O	L	W	7 g
2,5	666100	8	13	5	100	-	12
5	666250	0	23	5	150	-	94
B							
2,5	665040	8	13	1	75	-	12
3	665050	7	13	1	100	-	23

Handle-fitted keys

- Blue acetate handle.
- Burnished presentation.

