

ShrinkKit 321 is a family of three heat shrink tubing assortments in attractive and handy assembly kits. The range consists of ShrinkKit 321 Universal, ShrinkKit 321 Basic and ShrinkKit 321-A (a dual wall tubing). With their ideal shrink ratio of 3:1 these products replace many differently sized tubing solutions by fitting almost any heat shrink requirements. Choosing the required product is simplicity itself as the tubings are clearly identified by size, length and content printed on every compartment of the assortment boxes.



ShrinkKit 321 - Kits with optimised 3:1 shrink ratio.

ShrinkKit 321 Universal

Features and Benefits

The attractive and reusable kit is the solution for almost every heat shrink task. The big variety of sizes, colours and lengths offers a wide number of applications: insulation, bend protection or identification. The 3:1 shrink ratio can easily cope with substrates of varying diameter.

Content

This kit contains a range of general purpose tubing lengths clearly sorted in various sizes and colours. Its ideal shrink ratio of 3:1 replaces many differently sized tubings. The application range from 1 mm to 20 mm can be covered with ShrinkKit 321 Universal.



The right tubing size at hand for any application: ShrinkKit 321 Universal, ShrinkKit 321-A and ShrinkKit 321 Basic.

ShrinkKit 321 Universal

**New Standard:
Shrink Ratio 3:1**



Shrink ratio 3:1 for a wider range of application.

Material Data

Material	Polyolefin, cross-linked (POX)
Shrink Ratio	3:1
Longitudinal change after shrinkage	+5%/-10% max.
Minimum Shrink Temperature	+90 °C
Operating Temperature	-55 °C to +135 °C
Dielectric Strength	20 kV/mm according to ASTM D 2671
Flammability	self-extinguishing (except for transparent)



*The right tubing size at hand for any application:
ShrinkKit 321 Universal, ShrinkKit 321-A and
ShrinkKit 321 Basic.*

Technical Table

Article-No.	Comp.	Supplied Ø D	Recov. Ø d	Length (L)	Colour	Number of tubes
380-03002 ShrinkKit 321 Universal Pack Cont.	1	6	2	60	Black (BK)	50
	2	12	4	100	Black (BK)	15
	3	24	8	200	Black (BK)	10
	4	6	2	60	Green-Yellow (GNYE)	50
	5	3	1	50	Transparent (CL)	100
	6	3	1	50	Black (BK)	100
	7	12	4	100	Transparent (CL)	15
	8	12	4	100	Red (RD)	15
	9	3	1	50	Red (RD)	100
	10	3	1	40	Blue (BU)	100
	11	3	1	40	Green-Yellow (GNYE)	100
	12	1.5	0.5	40	Black (BK)	75
	12	1.5	0.5	40	Green-Yellow (GNYE)	75
	13	6	2	60	Blue (BU)	50
	14	6	2	60	Red (RD)	50
	15	6	2	60	Transparent (CL)	50
	16	12	4	170	Green-Yellow (GNYE)	10
	17	12	4	170	Blue (BU)	10

All dimensions in mm. Subject to technical changes.