

FLKM 14-PA-SLC500/IN

Order No.: 2293462

The illustration shows version FLKM 14-PA-SLC500/OUT



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2293462>

VARIOFACE front adapter, 2 x 8 channels can be connected, for Allen-Bradley SLC 500, 1746 IA16, IB16, ITB16 and IN16

Commercial data

GTIN (EAN)	4017918108861
Note	Made-to-order
sales group	I603
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.0574 KG
Catalog page information	Page 192 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
06/04/2007



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Connection type, plug connector	Flat-ribbon cable plug connector in acc. with IEC 60603-13
Number of plug connectors	2

No. of positions, plug connector	14
Number of positions	14
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Mounting position	Any
Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Max. permissible current	1 A (per path)
Max. permissible total current	2 A (Per Byte, for supply via connector)
Pollution degree	1
Surge voltage category	II
Supported controller	ALLEN-BRADLEY SLC 500
Supported I/O card	1746 IA16
	1746 IB16
	1746 ITB16
	1746 IN16


Certificates / Approvals



Certification CUL, GOST, UL

Diagrams/Drawings

Circuit diagram



Connection scheme FLKM 14-PA-SLC500/IN

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;