

RoHS Compliant



US-842

USB 8xRS422/485 1MBaud

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Description

USB to Serial providing 8 RS422/485 serial ports. Up to 921,600 data transfer rates and the 128 byte deep transmit and 384 byte receive FIFOs, coupled with 1Mbit line drivers deliver uncompromising performance on your laptop/PC.

USB to serial is the quick low cost way to connect your computer to a serial comms enabled device. Boost software gives industry leading functionality and compatibility.


These products do away with traditional issues with USB technology so you can buy with confidence!

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

Features

- 8 port RS422/485
- USB
- 128 Byte Tx and 384 Byte Rx FIFOs
- Up to 921,600 Baud
- 8xDB9 connector (9 Pin Male) Industrial high retention USB connector
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



US-842:
USB 8xRS422/485
1MBaud

Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit and 64 bit editions
- Windows Vista 32 bit and 64 bit editions
- Windows XP 32 bit & 64 bit editions

64Bit
Driver

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



ORDER

Description

USB 8xRS422/485 1MBaud
USB Cable & Power Supply

Code

US-842

US-842: Full Specification

RS422/485 Pinout (9 pin)

1 5

6 9