

NX3225SA

For Automotive


■ Features

A small surface-mount type crystal unit, ideal for automotive applications.

- With a well established reputation for reliability, this product is best suited for automotive equipment.
- Stable start-up characteristic even under extremely severe environmental conditions.
- Excellent environmental characteristics, including heat, vibration and shock resistance.
- Lead-free. Meets the requirements for re-flow profiling using lead-free solder.
- Conforms to AEC-Q200.

Pb Free

RoHS Compliant
Directive 2011/65/EU
Directive (EU) 2015/863



■ Specifications

Item	Model	NX3225SA	
		Standard	Optional
Nominal Frequency (MHz)		12 to 50	12 to 50
Overtone Order		Fundamental	Fundamental
Frequency Tolerance (25 ±3 °C)		±15 × 10 ⁻⁶	±15 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)		±50 × 10 ⁻⁶	±50 × 10 ⁻⁶
Operating Temperature Range (°C)		-40 to +125	-40 to +125
Storage Temperature Range (°C)		-40 to +125	-40 to +125
Equivalent Series Resistance		Refer to *1	Refer to *1
Level of Drive (μW)		10 (Max. 200)	10 (Max. 200)
Load Capacitance (pF)		8	6 to 32
Frequency Aging (+25 °C)		---	Max. ±3 × 10 ⁻⁶ / year *2
Specifications Number		STD-CRS-2	Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*2 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (38.400000MHz 6digits), S1:Fundamental or S3:3rd Overtone

- Operating Temperature Range (-40 to +125°C) - Frequency versus Temperature Characteristics (±50×10⁻⁶)


- Frequency Tolerance (±15×10⁻⁶) - Load Capacitance (8pF)

NX3225SA

38.400000MHz

S1-40125-50-15-8

■ Dimensions



*1 Equivalent Series Resistance

Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
12 to 20	120
20 to 50	100

If you have any other requests, NDK will study it.