

### Features and Benefits

- Easy to use, clip-on detachable head
- Pre-moulded plug and play cable supplied to connect to motorised head
- Metal manual operating lever for strength and stability
- The motorised head can be retrofitted to other manufacturers' valve bodies.

### Description

A 240V two port zone valve for use in heating systems to isolate zones or equipment when the motor is de-energised. The valve is supplied complete with a pre-made moulded cable to plug straight into motorised head, allowing easy connection and disconnection for maintenance. The RWC two port zone valve features a unique detachable motorised head with a robust metal manual actuating lever, and is interchangeable with other leading manufacturers' valve bodies, mounted on a high quality brass body to ensure a long operating life and total installation flexibility.

### Specifications

Power supply	220-240V, 50/60Hz, 5W
System fuse rating	3A maximum
Auxiliary switch rating	3A 250VAC
Water temp	5°C to 88°C
Max. differential pressure	0.69 bar
Cable length	1m
Max. pressure	6 bar

### Product Codes


ZONE250205	22mm zone valve with detachable head and pre-wired cable
------------	--

### Approvals

Electro-Magnetic Compatibility Directive  
2004/108/EC  
Low Voltage Directive 2006/95/EEC  
EC Marking Directive 93/68/EEC



### Dimensions



All dimensions are in mm

## Reliance Water Controls Ltd

A Reliance Worldwide Company

Worcester Road, Evesham, Worcestershire, WR11 4RA, UK. UK – Freephone: 0800 389 5931

Freefax: 0800 389 5932 Outside UK – Tel: +44 (0)1386 712400 Fax: +44 (0)1386 712401 Email: sales@rwc.co.uk

Reliance reserves the right to make changes to the product and the information contained in this leaflet at any time. © Reliance Water Controls Ltd 2013