

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35720-1110](#)
Status: **Active**
Overview: [Quick-Disconnect Terminals](#)
Description: 5.21mm Slip-On Receptacle Terminal, Quick Disconnect , 0.50mm Tab Thickness, Wire Range 22-24 AWG (0.33-0.20mm²), Post-Tin Plated

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-35703-001 \(PDF\)](#)
[Packaging Specification PK-35720-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Quick Disconnects
Series	35720
Crimp Quality Equipment	Yes
Insulated	No
Overview	Quick-Disconnect Terminals
Product Name	Slip-On
Type	Quick Disconnect
UPC	756054255117

Physical

Barrel Type	Open
Gender	Female
Glow-Wire Compliant	No
Insulation	None
Lock to Mating Part	Yes
Material - Metal	Brass
Net Weight	0.493/g
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	5.21mm
Temperature Range - Operating	-40°C to +105°C
Wire Insulation Diameter	2.50mm max.
Wire Size AWG	22, 24
Wire Size mm²	0.20 - 0.35


Electrical

Voltage - Maximum	250V
-------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35720-001
Product Specification	PS-35703-001
Sales Drawing	SD-35720-11*0



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35720Series](#)

Use With
5.21mm Tab

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

35720-1110