



PRODUCT NUMBER
70233-XXX
70233-XXYLF



mat'l code				--		tolerances unless otherwise specified				CUSTOMER				 www.fciconnect.com								
ltr	ecn no.	dr	date	linear	0.X ±0.3				COPY								title METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT					
AF	V06-0498	DCH	2006-05-30		0.XX ±0.13																	
AG	DG09-0256	TER	2009-08-19		.XXX ±.051																	
-	-	-	-	angles	0° ±2°																	
AB	V04-0554	TAB	06/07/04	dr	T.BRUNGARD 11/19/99								product family				METRAL				code	
AC	V05-0079	HTB	02/03/05	enrg	M.STRAWER 11/19/99								size				dwg no				213	
AD	V05-0030	DAI	02/10/05	chr	M.STRAWER 11/19/99				scale 2:1				A				70233				sheet 1 of 9	
AE	V05-1030	LP	11/18/05	appd	M.STRAWER 02/29/00																	
sheet index		revision sheet		AG	AG	AG	AG	AG	AG	AG	AG	AG	AG									
				1	2	3	4	5	6	7	8	9										


This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCJ. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCJ. Copyright FCJ.



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE

SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
9	5.00	17.00
10	5.75	17.00
11	6.50	17.00
12	7.25	17.00
13	8.25	4.30
14	8.25	13.60
15	8.25	17.00
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00

mat'l code				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com		
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT		
AG					0.XX ±0.13	projection 	product family METRAL			
					.XXX ±.051					
				angles	0° ±2°	 MM scale 1:1		code		
				dr	T.BRUNGARD 11/19/99			size		dwg no 70233
				enrg	M.STRAWSE 11/19/99	sheet		213		
				chr	M.STRAWSE 11/19/99	sheet		2		
				appd	M.STRAWSE 02/29/00					
sheet	revision									
index	sheet									

cage code 22526

Pro/E

PDM: Rev:AG

STATUS:Released

Printed: Feb 20, 2010



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X10 SEE NOTE 11 LEAD FREE OPTION	D	1	1	1	1	1	1	1	1	1	1
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X15 SEE NOTE 11 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X20 SEE NOTE 11 LEAD FREE OPTION	D	5	5	5	5	5	5	5	5	5	5
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X16 SEE NOTE 11 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X21 SEE NOTE 11 LEAD FREE OPTION	D	5	5	5	5	5	5	5	5	5	5
	C	5	5	5	5	5	5	5	5	5	5
	B	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X17 SEE NOTE 11 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X22 SEE NOTE 11 LEAD FREE OPTION	D	5	5	5	5	5	5	5	5	5	5
	C	5	5	5	5	5	5	5	5	5	5
	B	5	5	5	5	5	5	5	5	5	5
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X18 SEE NOTE 11 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X23 SEE NOTE 11 LEAD FREE OPTION	D	7	7	7	7	7	7	7	7	7	7
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X19 SEE NOTE 11 LEAD FREE OPTION	D	4	4	4	4	4	4	4	4	4	4
	C	4	4	4	4	4	4	4	4	4	4
	B	4	4	4	4	4	4	4	4	4	4
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X24 SEE NOTE 11 LEAD FREE OPTION	D	8	8	8	8	8	8	8	8	8	8
	C	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7
	A	8	8	8	8	8	8	8	8	8	8

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCJ www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3			COPY		title	
AG					0.XX ±0.13			projection		METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT	
					.XXX ±.051						
				angles	0° ±2°					product family	
				dr	T.BRUNGARD		11/19/99		METRAL		code
				enrg	M.STRAWSE		11/19/99		size		213
				chr	M.STRAWSE		11/19/99		dwg no		sheet
				appd	M.STRAWSE		02/29/00		A		3
sheet		revision									
index		sheet									



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X25 SEE NOTE 11 LEAD FREE OPTION	D	7	7	7	7	7	7	7	7	7	7
	C	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7
	A	7	7	7	7	7	7	7	7	7	7
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X26 SEE NOTE 11 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X27 SEE NOTE 11 LEAD FREE OPTION	D	7	7	7	7	7	7	7	7	7	7
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	5	5	5	5	5	5	5	5	5	5
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X28 SEE NOTE 11 LEAD FREE OPTION	D	7	7	7	7	7	7	7	7	7	7
	C	5	5	5	5	5	5	5	5	5	5
	B	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X29 SEE NOTE 11 LEAD FREE OPTION	D	8	8	8	8	8	8	8	8	8	8
	C	8	8	8	8	8	8	8	8	8	8
	B	8	8	8	8	8	8	8	8	8	8
	A	8	8	8	8	8	8	8	8	8	8

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X30 SEE NOTE 11 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	11	11	11	11	11	11	11	11	11	11
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X31 SEE NOTE 11 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	9	9	9	9	9	9	9	9	9	9
	B	9	9	9	9	9	9	9	9	9	9
	A	9	9	9	9	9	9	9	9	9	9
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X32 SEE NOTE 11 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	9	9	9	9	9	9	9	9	9	9
	B	9	9	9	9	9	9	9	9	9	9
	A	11	11	11	11	11	11	11	11	11	11
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X33 SEE NOTE 11 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	11	11	11	11	11	11	11	11	11	11
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X34 SEE NOTE 11 LEAD FREE OPTION	D	12	12	12	12	12	12	12	12	12	12
	C	11	11	11	11	11	11	11	11	11	11
	B	11	11	11	11	11	11	11	11	11	11
	A	12	12	12	12	12	12	12	12	12	12

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X35 SEE NOTE 11 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	11	11	11	11	11	11	11	11	11	11
	B	11	11	11	11	11	11	11	11	11	11
	A	11	11	11	11	11	11	11	11	11	11
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X36 SEE NOTE 11 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	10	10	10	10	10	10	10	10	10	10
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X37 SEE NOTE 11 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	9	9	9	9	9	9	9	9	9	9
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X38 SEE NOTE 11 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	9	9	9	9	9	9	9	9	9	9
	B	9	9	9	9	9	9	9	9	9	9
	A	9	9	9	9	9	9	9	9	9	9
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X39 SEE NOTE 11 LEAD FREE OPTION	D	12	12	12	12	12	12	12	12	12	12
	C	12	12	12	12	12	12	12	12	12	12
	B	12	12	12	12	12	12	12	12	12	12
	A	12	12	12	12	12	12	12	12	12	12

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCJ www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT
AG					0.XX ±0.13				
					.XXX ±.051				
				angles	0° ±2°	MM	scale	product family	METRAL
				dr	T.BRUNGARD 11/19/99				
				enrg	M.STRAWSE 11/19/99				
				chr	M.STRAWSE 11/19/99	A	70233	code	213
				appd	M.STRAWSE 02/29/00				
sheet	revision							size	dwg no
index	sheet								



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X40 SEE NOTE 11 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	4	4	4	4	4	4	4	4	4	4
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X45 SEE NOTE 11 LEAD FREE OPTION	D	1	1	1	1	1	1	1	1	1	1
	C	2	2	2	2	2	2	2	2	2	2
	B	3	3	3	3	3	3	3	3	3	3
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X50 SEE NOTE 11 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	8	8	8	8	8	8	8	8	8	8
	A	6	6	6	6	6	6	6	6	6	6

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT
AG					0.XX ±0.13				
					.XXX ±0.051				
				angles	0° ±2°	MM	scale	product family	METRAL
				dr	T.BRUNGARD 11/19/99				
				enrg	M.STRAWSE 11/19/99				
				chr	M.STRAWSE 11/19/99	A	70233	code	213
				appd	M.STRAWSE 02/29/00				
sheet	revision							size	dwg no
index	sheet								



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X55 SEE NOTE 11 LEAD FREE OPTION	D	5	5	5	5	5	5	5	5	5	5
	C	6	6	6	6	6	6	6	6	6	6
	B	7	7	7	7	7	7	7	7	7	7
	A	8	8	8	8	8	8	8	8	8	8

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X56 SEE NOTE 11 LEAD FREE OPTION	D	20	20	20	20	20	20	20	20	20	20
	C	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X57 SEE NOTE 11 LEAD FREE OPTION	D	8	8	8	8	8	8	8	8	8	8
	C	8	8	8	8	8	8	8	8	8	8
	B	14	14	14	14	14	14	14	14	14	14
	A	14	14	14	14	14	14	14	14	14	14

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X58 SEE NOTE 11 LEAD FREE OPTION	D	20	20	20	20	20	20	20	20	20	20
	C	20	20	20	20	20	20	20	20	20	20
	B	20	20	20	20	20	20	20	20	20	20
	A	20	20	20	20	20	20	20	20	20	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X59 SEE NOTE 11 LEAD FREE OPTION	D	8	8	8	8	8	8	8	8	8	8
	C	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X60 SEE NOTE 11 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10
	B	12	12	12	12	12	12	12	12	12	12
	A	10	10	10	10	10	10	10	10	10	10

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X61 SEE NOTE 11 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	12	12	12	12	12	12	12	12	12	12

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X62 SEE NOTE 11 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	9	9	9	9	9	9	9	9	9	9
	B	9	9	9	9	9	9	9	9	9	9
	A	10	10	10	10	10	10	10	10	10	10

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X63 SEE NOTE 11 LEAD FREE OPTION	D	15	15	15	15	15	15	15	15	15	15
	C	11	11	11	11	11	11	11	11	11	11
	B	11	11	11	11	11	11	11	11	11	11
	A	11	11	11	11	11	11	11	11	11	11

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X64 SEE NOTE 11 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	11	11	11	11	11	11	11	11	11	11
	B	12	12	12	12	12	12	12	12	12	12
	A	11	11	11	11	11	11	11	11	11	11

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X65 SEE NOTE 11 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	10	10	10	10	10	10	10	10	10	10
	B	11	11	11	11	11	11	11	11	11	11
	A	12	12	12	12	12	12	12	12	12	12

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X66 SEE NOTE 11 LEAD FREE OPTION	D	21	21	21	21	21	21	21	21	21	21
	C	11	11	11	11	11	11	11	11	11	11
	B	11	11	11	11	11	11	11	11	11	11
	A	11	11	11	11	11	11	11	11	11	11

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X67 SEE NOTE 11 LEAD FREE OPTION	D	12	12	12	12	12	12	12	12	12	12
	C	12	12	12	12	12	12	12	12	12	12
	B	15	15	15	15	15	15	15	15	15	15
	A	15	15	15	15	15	15	15	15	15	15

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X68 SEE NOTE 11 LEAD FREE OPTION	D	21	21	21	21	21	21	21	21	21	21
	C	21	21	21	21	21	21	21	21	21	21
	B	21	21	21	21	21	21	21	21	21	21
	A	21	21	21	21	21	21	21	21	21	21

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X69 SEE NOTE 11 LEAD FREE OPTION	D	12	12	12	12	12	12	12	12	12	12
	C	11	11	11	11	11	11	11	11	11	11
	B	11	11	11	11	11	11	11	11	11	11
	A	11	11	11	11	11	11	11	11	11	11

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT
AG					0.XX ±0.13				
					.XXX ±0.051				
				angles	0° ±2°	MM	scale	product family	METRAL
				dr	T.BRUNGARD 11/19/99				
				enrg	M.STRAWSE 11/19/99				
					chr	M.STRAWSE 11/19/99	A	size	dwg no
					appd	M.STRAWSE 02/29/00			
sheet	revision							70233	code
index	sheet								
								213	
								sheet	
								6	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X70 SEE NOTE 11 LEAD FREE OPTION	D	4	4	4	4	4	4	4	4	4	4
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X71 SEE NOTE 11 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	1	1	1	1	1	1	1	1	1	1
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X72 SEE NOTE 11 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	4	4	4	4	4	4	4	4	4	4
	B	4	4	4	4	4	4	4	4	4	4
	A	19	19	19	19	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X73 SEE NOTE 11 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	3	3	3	3	3	3	3	3	3	3
	B	2	2	2	2	2	2	2	2	2	2
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X74 SEE NOTE 11 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X75 SEE NOTE 11 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X76 SEE NOTE 11 LEAD FREE OPTION	D	19	19	19	19	19	19	19	19	19	19
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	19	19	19	19	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X77 SEE NOTE 11 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2
	C	3	3	3	3	3	3	3	3	3	3
	B	19	19	19	19	19	19	19	19	19	19
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X78 SEE NOTE 11 LEAD FREE OPTION	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1
	B	3	3	3	3	3	3	3	3	3	3
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X79 SEE NOTE 11 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X80 SEE NOTE 11 LEAD FREE OPTION	D	8	8	8	8	8	8	8	8	8	8
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X81 SEE NOTE 11 LEAD FREE OPTION	D	7	7	7	7	7	7	7	7	7	7
	C	7	7	7	7	7	7	7	7	7	7
	B	5	5	5	5	5	5	5	5	5	5
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X82 SEE NOTE 11 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	8	8	8	8	8	8	8	8	8	8
	B	8	8	8	8	8	8	8	8	8	8
	A	20	20	20	20	20	20	20	20	20	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X83 SEE NOTE 11 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	7	7	7	7	7	7	7	7	7	7
	B	6	6	6	6	6	6	6	6	6	6
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X84 SEE NOTE 11 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7
	A	7	7	7	7	7	7	7	7	7	7

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCJ	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
AG				linear	0.XX ±0.13	projection		title	
				angles	.XXX ±.051			METRAL SIGNAL HEADER	
				dr	T.BRUNGARD 11/19/99			2 MOD, 4 ROW PRESS-FIT	
				enrg	M.STRAWSE 11/19/99	MM		product family	
				chr	M.STRAWSE 11/19/99	scale		METRAL	
				appd	M.STRAWSE 02/29/00	1:1		code	
sheet	revision							213	
index	sheet							sheet	
								7	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X85 SEE NOTE 11 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	7	7	7	7	7	7	7	7	7	7
70233-X86 SEE NOTE 11 LEAD FREE OPTION	D	20	20	20	20	20	20	20	20	20	20
	C	5	5	5	5	5	5	5	5	5	5
	B	5	5	5	5	5	5	5	5	5	5
	A	20	20	20	20	20	20	20	20	20	20
70233-X87 SEE NOTE 11 LEAD FREE OPTION	D	6	6	6	6	6	6	6	6	6	6
	C	7	7	7	7	7	7	7	7	7	7
	B	20	20	20	20	20	20	20	20	20	20
	A	7	7	7	7	7	7	7	7	7	7
70233-X88 SEE NOTE 11 LEAD FREE OPTION	D	5	5	5	5	5	5	5	5	5	5
	C	5	5	5	5	5	5	5	5	5	5
	B	7	7	7	7	7	7	7	7	7	7
	A	5	5	5	5	5	5	5	5	5	5
70233-X89 SEE NOTE 11 LEAD FREE OPTION	D	7	7	7	7	7	7	7	7	7	7
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X90 SEE NOTE 11 LEAD FREE OPTION	D	12	12	12	12	12	12	12	12	12	12
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	10	10	10	10	10	10	10	10	10	10
70233-X91 SEE NOTE 11 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	11	11	11	11	11	11	11	11	11	11
	B	9	9	9	9	9	9	9	9	9	9
	A	11	11	11	11	11	11	11	11	11	11
70233-X92 SEE NOTE 11 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	12	12	12	12	12	12	12	12	12	12
	B	12	12	12	12	12	12	12	12	12	12
	A	21	21	21	21	21	21	21	21	21	21
70233-X93 SEE NOTE 11 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	11	11	11	11	11	11	11	11	11	11
	B	10	10	10	10	10	10	10	10	10	10
	A	11	11	11	11	11	11	11	11	11	11
70233-X94 SEE NOTE 11 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	11	11	11	11	11	11	11	11	11	11
	B	11	11	11	11	11	11	11	11	11	11
	A	11	11	11	11	11	11	11	11	11	11

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70233-X95 SEE NOTE 11 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	11	11	11	11	11	11	11	11	11	11
70233-X96 SEE NOTE 11 LEAD FREE OPTION	D	21	21	21	21	21	21	21	21	21	21
	C	9	9	9	9	9	9	9	9	9	9
	B	9	9	9	9	9	9	9	9	9	9
	A	21	21	21	21	21	21	21	21	21	21
70233-X97 SEE NOTE 11 LEAD FREE OPTION	D	10	10	10	10	10	10	10	10	10	10
	C	11	11	11	11	11	11	11	11	11	11
	B	21	21	21	21	21	21	21	21	21	21
	A	11	11	11	11	11	11	11	11	11	11
70233-X98 SEE NOTE 11 LEAD FREE OPTION	D	9	9	9	9	9	9	9	9	9	9
	C	9	9	9	9	9	9	9	9	9	9
	B	11	11	11	11	11	11	11	11	11	11
	A	9	9	9	9	9	9	9	9	9	9
70233-X99 SEE NOTE 11 LEAD FREE OPTION	D	11	11	11	11	11	11	11	11	11	11
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	10	10	10	10	10	10	10	10	10	10

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3			projection		title METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT	
AG					0.XX ±0.13						
					.XXX ±.051						
				angles	0° ±2°				product family METRAL	code 213	
				dr	T.BRUNGARD 11/19/99						
				enrg	M.STRAWSE 11/19/99						
					chr	M.STRAWSE 11/19/99			size A	sheet 8	
					appd	M.STRAWSE 02/29/00					
sheet index	revision	sheet									



PRODUCT NUMBER
70233-XY Y
70233-XY YLF

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON PRESS-FIT TAIL:
55422 -XY Y IS SnPb
55422-XY YLF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE.

- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.

- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXPLF

- PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-073

- AFTER INSERTION INTO CIRCUIT BOARD WITH
QUALIFIED TOOL.
- A PLATING HAS Au FLASH IN PRESS FIT
AREA (LEAD FREE).
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.

ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.

- FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.
EXAMPLE: 70233-X01LF

PLATING IN CONTACT AREA		
DASH NUMBER	PERFORMANCE LEVEL	NOTES
-AYY	TELCORDIA CO	SEE NOTE 9
-N1YY	TELCORDIA CO (NXT)	-
-N5YY	TELCORDIA UE (NXT)	-
-1YY	TELCORDIA CO	-
-2YY	TELECOM CLASS	-
-3YY	IEC CLASS I	-
-5YY	TELCORDIA UE	-
-AYYLF	TELCORDIA CO	SEE NOTE 10
-N1YYLF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 10
-N5YYLF	TELCORDIA UE (NXT)	SEE NOTE 10
-1YYLF	TELCORDIA CO IEC CLASS I	SEE NOTE 10
-2YYLF	TELECOM CLASS	SEE NOTE 10
-5YYLF	TELCORDIA UE	SEE NOTE 10

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT	
AG					0.XX ±0.13	projection			
					.XXX ±.051	MM			
				angles	0° ±2°	scale		product family METRAL code	
				dr	T.BRUNGARD	11/19/99	size		213
				enrg	M.STRAWSE	11/19/99	dwg no		sheet
				chr	M.STRAWSE	11/19/99	A		9
				appd	M.STRAWSE	02/29/00	70233		
sheet	revision								
index	sheet								

cage code 22526

Pro/E

PDM: Rev:AG

STATUS:Released

Printed: Feb 20, 2010