

3


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA13-A THRU PCA13-Z	'A' THRU 'Z'	30	300	1	10	.130" - .150"
PCA13-A-J	'A' - 'J' [3 EA.]	30	300	1	10	.130" - .150"
PCA13-K-T	'K' - 'T' [3 EA.]	30	300	1	10	.130" - .150"
PCA13-U-Z	'U' - 'Z' [3 EA.]	30	300	1	10	.130" - .150"
PCA13-0 THRU PCA13-9	'0' THRU '9'	30	300	1	10	.130" - .150"
PCA13-0-9	'0' - '9' [3 EA.]	30	300	1	10	.130" - .150"
PCA13-MIN	' - '	30	300	1	10	.130" - .150"
PCA13-PLS	' + '	30	300	1	10	.130" - .150"

3

NOTES:

1. COLOR: WHITE WITH BLACK LEGENDS.
2. MILLIMETERS ARE IN [].



CAD FILENAME/LAYERS

100281DF-DC-C10346/03C

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
PCA13-* CLIP-ON WIRE MARKERUNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .062 (XXX) ± .015
(.XX) ± .031 ANGLES ±UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

2	8/11/10	RVU		UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.	6079	R			
1	7-15-07	RVU		ADDED TOLERANCE AND REVISED TABLE.	4881	R			
0	10-5-06	RVU		DRAWING RELEASE	4715	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	

DRAWN BY
RVU

MAT'L:

DATE
9-5-04WHITE MARKER
- ACETAL

CHK'D

SCALE

DRAWING NO.

C10346

DWG
A
SIZE