




MARERIAL&FINISH
insulator:PBT Glass Fiber(UL94V-0)
Contact:Brass
Contact:Gold-Plated Over Nickel.
SPECIFICATIONS
Current Rating:1A AC,DC
Voltage Rating:250V AC,DC
Temperature Range:-40°C TO+105°C
Contact Resistance:20mΩ Min
Insulation Resistance:1000mΩ Min
Withstanding Voltage:500V AC/Min

NUMBER OF POSITIONS	DIMENSION	
	A	B
06	5.08	12.32
08	7.62	14.86
10	10.16	17.40
12	12.7	19.94
14	15.24	22.48
16	17.78	25.02
18	20.32	27.56
20	22.86	30.10
24	27.94	35.18
26	30.48	37.72
28	33.02	40.26
30	35.56	42.80
34	40.64	47.88
40	48.26	55.5
50	60.96	68.20
60	73.66	80.90
64	78.74	85.98

UNLESS OTHERWISE SPECIFIED TOLERANCE :		CnC Tech, LLC Industrial Cable and Connector Technology				
X.	±0.20	ANGLES : ±2°				
X.X	±0.15	DO NOT SCALE DRAWING				
X.XX	±0.10					
DRAWN BY	Kevin		PART NO. 3030-01-XX-0104			
CHECKED BY		SIZE A	UNIT MM	TITLE 2.54/DC		REV A0
APPROVED BY	FALLU@mp		SCALE	THIRD ANGLE PROJECTION  		PAGE 1 OF 1
DWG NO.				ITEM NO.		DATE 2005/07/17