

DA Series

Miniature Single Pole Rocker Switches

Features/Benefits

- Nice actuator styling with multiple options
- Guards to prevent accidental actuation
- Momentary and maintained functions
- IP65 splash proof rubber boot option
- RoHS compliant

Typical Applications

- Small appliances
- Computers and peripherals
- Medical instrumentation



C&K US UL 61058-1

Specifications

CONTACT RATING:
16 AMPS @ 125 VAC, 1/3 HP;
10 AMPS @ 250 VAC, 1/2 HP.
10 AMPS @ 125 VAC, 6 AMPS @ 250 VAC.
ELECTRICAL LIFE: 10,000 make and break cycles at full load.
INSULATION RESISTANCE: $10^8 \Omega$ min.
DIELECTRIC STRENGTH: 1,500 VRMS @ sea level.
OPERATING TEMPERATURE: -20°C to +85°C

Materials

HOUSING AND ACTUATOR: 6/6 nylon (UL94V-2), black, matte finish.
ILLUMINATED ACTUATOR: Polycarbonate, matte finish.
CENTER CONTACTS: Silver plated, copper alloy.
END CONTACTS: Silver plated.
ALL TERMINALS: Silver plated, copper alloy.

NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages G-58 through G-60. For additional options not shown in catalog, consult Customer Service Center.

Switch Function DA101 SPDT On-None-On DA102 SPST On-None-Off DA103 SPDT On-Off-On	Actuator J1 Rocker J2 Two-tone rocker *J3 Illuminated rocker J4 Circle, illuminated rocker J5 Oval, illuminated rocker Actuator Color 1-5 See Chart on Page G-59 *R Red, illuminated *A Amber, illuminated *G Green, illuminated	Mounting Style/Color S2 Snap-in, black S1 Snap-in, white B2 Recessed snap-in bracket, black G2 Guard, black Termination 15 .187" quick connect 17 Solder lug 02 Thru-hole A Right angle Actuator Marking (NONE) No marking D ON-OFF H "O I" - international ON-OFF N Large dot P "O -" international ON-OFF	Contact Rating QF Silver Lamp Rating (NONE) No lamp 6 LED 7 125 VAC neon 8 250 VAC neon
---	---	---	--



* "J3" illuminated switches are not available with actuator markings



DA Series

Miniature Single Pole Rocker Switches

SWITCH FUNCTION


NO. POLES	MODEL NO.	SWITCH FUNCTION			CONNECTED TERMINALS			SCHEMATIC
								
		C&K marking on opposite side			C&K marking on opposite side			
SP	DA101	ON	NONE	ON				
	DA102	ON	NONE	OFF	2-3	N/A	2-1	 For 7 & 8 Illuminated Versions Only
	DA103	ON	OFF	ON				 For 6 Illuminated Versions Only

Shown in Pos. 1

ACTUATOR

J1 ROCKER


*J3 ILLUMINATED ROCKER



NOTE: J3 actuator available with DA102 switch functions, 7&8 lamp ratings and not available with O2 and A termination options.

* J3 actuator not available with markings


J2 TWO-TONE ROCKER



NOTE:

1. Available with DA102 switch function only.
2. Available with None or P actuator marking options only.

Rocker



Third Angle Projection


Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change

www.ck-components.com

DA Series Miniature Single Pole Rocker Switches


ACTUATOR

J4 CIRCLE, ILLUMINATED ROCKER



NOTE: Available with DA102 switch function and 7 & 8 lamp ratings combinations only. Not available with O2 and A termination options.

J5 OVAL, ILLUMINATED ROCKER




NOTE: Available with DA102 switch function and 6 lamp rating combinations only. Not available with O2 and A termination options.

ACTUATOR COLOR

	OPTION CODE	ACTUATOR COLOR
	2	BLACK
J1 only	1	WHITE
	3	RED
	R	RED, ILLUMINATED
	A	AMBER, ILLUMINATED
J3, J4, J5 only	G	GREEN, ILLUMINATED





	OPTION CODE	ACTUATOR COLOR TOP	ACTUATOR COLOR BOTTOM
	1	WHITE	RED
J2 only	2	WHITE	BLACK
	3	RED	WHITE
	4	BLACK	WHITE
	5	BLACK	RED



MOUNTING STYLE/COLOR


S2 SNAP-IN, BLACK

S1 SNAP-IN, WHITE



NOTE: Available with DA10X switch functions only.


S2, S1 & G2 PANEL MOUNTING



PANEL THICKNESS	"X"	"Y"
0.030-0.049 (0,75-1,25)	0.756-.004 (19,2-0,1)	0.512+.004 (13,0+0,1)
0.049-0.079 (1,25-2,0)	0.764-.004 (19,4-0,1)	0.512+.004 (13,0+0,1)
0.079-0.118 (2,0-3,0)	0.779-.004 (19,8-0,1)	0.512+.004 (13,0+0,1)


Actuator shown in Pos. 1

B2 RECESSED SNAP-IN BRACKET, BLACK



NOTE: Available with DA10X switch functions only.

B2 PANEL MOUNTING



PANEL THICKNESS	"Y"
0.030-0.049 (0,75-0,25)	1.068 (27,13)
0.049-0.079 (1,25-2,0)	1.076 (27,33)
0.079-0.118 (2,0-3,0)	1.092 (27,74)



Dimensions are shown: Inches (mm)

Specifications and dimensions subject to change


www.ck-components.com




DA Series Miniature Single Pole Rocker Switches

TERMINATION


15 .187" QUICK CONNECT



17 SOLDER LUG




02* THRU-HOLE



* NOTE - O2 and A termination options not offered with J3, J4 or J5 actuator options.

A* RIGHT ANGLE



ACTUATOR MARKING

NONE NO MARKING



D ON-OFF




H O I



N LARGE DOT



P O -



All models shown in Pos. 1
Markings not available with J3 actuator

NOTE: Orientation of actuator marking and terminals.

CONTACT MATERIAL

OPTION CODE	CONTACT AND TERMINAL MATERIAL	RATINGS	
QF	SILVER	POWER	16 AMPS @ 125 VAC; 1/3 HP; 10 AMPS @ 250 VAC; 1/2 10 AMPS @ 125 VAC, 6 AMPS @ 250 VAC

* Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

LAMP RATING

(NONE) NO LAMP



6 LED RATING @ 10 mA $V_F=1.85V$

7 125 VAC 33kΩ NEON

8 250 VAC 150kΩ NEON

ACCESSORIES

216C00000 IP65 SPLASH PROOF RUBBER BOOT



Third Angle
Projection

Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change

www.ck-components.com

