

**Mallory Sonalert Products, Inc.**


Part #:

SCE120MA3SP1B**Sales Outline Drawing**

Revision:

C**Specifications:**

Sound Level Category	Medium
Mode of Operation	Slow Pulse @ 1 PPS
Voltage Rating	48 to 120 VAC
Frequency	2900 ± 500 Hz
Loudness @ 2 FT	75 to 85 dB(A) Typ.
Current Draw	40mA MAX
Housing Material	6/6 Nylon, Color: Black
Storage Temperature	-40° to +85° C
Operating Temperature	-40° to +85° C
Panel Mounting	Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole.
Knurled Nut	Used to attach part to panel. The max recommended torque is 10 in-lbs.
Weight (Typical)	1.6 oz (45g)
NEMA 3R, 4X, & 12	Approved with use of ACC03.
cUL Recognition	Supply voltage shall employ Transient Voltage Surge Suppression.
Options	Please contact factory.

Dimensions: Inches (mm)**cUL Recognized****ROHS Compliant**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mallory Sonalert:

<u>SCE048LD3CM1F</u>	<u>SCE120MA3SP1B</u>	<u>SCE120SD3CK1S</u>	<u>SCE120LD2CT1B</u>	<u>SCE028MD3DT8S</u>	
<u>SCE016MD3MV0W</u>	<u>SCE016MD3CK1F</u>	<u>SCE028LD3MG5S</u>	<u>SCE016LD3DP3S</u>	<u>SCE028LD2CT1F</u>	<u>SCE120MA3CTW</u>
<u>SCE028MD3SR4S</u>	<u>SCE016LD3CM1S</u>	<u>SCE028LD2CM4S</u>	<u>SCE016LD3MG3S</u>	<u>SCE016XD3MG5F</u>	<u>SCE028LD3DT7S</u>
<u>SCE028MD3CK1S</u>	<u>SCE016SD3DT8W</u>	<u>SCE028LD3SR3S</u>	<u>SCE028MD3DT5S</u>	<u>SCE120LA3CTW</u>	<u>SCE028LD2TT1S</u>