

Part Number: **5973602102F**

General Description	
Series	597
Configuration	1210 Package
Description	SMD LED 1210 B Sample Strip
Package Options	Sample Strip
Lamp Type	Single Color
LED Type	InGaN
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25Â°)	
Forward Current mA	20mA
Reverse Current	100 @ Vr =4V
Forward Current Pulsed	80mA
Derating	from 25Â° @ .33mA/Â°C
Operating Temperature	-55 - + 85
Storage Temperature	-55 - + 85

Operating Characteristics	
Color	Blue
Luminous Intensity Typical	5
Dominant Wavelength Typical	470nm
Power Dissipation Max	60mW



5973602102F

[check stock](#)



[This is a
RoHS Compliant Product.
To learn more click here](#)