




	RG 316/U Tinted Brown
	4814-BB-XX
Cap. pF/ft.	29.0
Nom. Imp. Ohms	50
Loss	.56 dB/ft @ 3 GHz Max.
Temperature	+200°C. (+392°F.) Max.

MATERIALS:

Connectors: Right Angle SMA (Male) & SMA (Male)
 Body – Passivated Stainless Steel, Contact: Gold Plated Brass
 Dielectric – Teflon
 Finish: Contact – Hard gold plated
 Body – Nickel plated
 Cable: See Tab Block Marking: “Pomona 4814-X-XX”

RATINGS:

Operating Voltage: 335 VRMS Max.

ORDERING INFORMATION: Model 4814-BB-XX

X=Cable Type (see table)

XX = Cable Lengths, Standard Lengths: 24” (610), 48” (1219) & 60” (1524).

Additional lengths can be quoted upon request.

Ordering Example: 4814-BB-24 Indicates 24” in length.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA