




TM-131 防塵ゴム

Sealing Rubber Gasket



特長

サイズ違いが豊富な防塵ゴムです。

用途

計装・制御盤・工作機械・家電・医療機器・家具・事務機器等

仕様

連続気泡につき防水には対応しておりません。場合によっては継目が入り、段差ができることがあります。

材質と処理 Material & Finish

材質 Material	処理 Finish
ラテックススポンジ Latex Sponge	黒色 Black

■ L 寸法許容差 L dimensional Tolerance

寸法範囲 size	100 以下 (100 or less)	100 を超え 200 以下 (Over 100, 200 or less)	200 を超え 500 以下 (Over 200, 500 or less)
許容差 Dimensional Tolerance	+5	+10	+25

※ 500 を超える寸法は L 寸法の +5% です。
Size over 500 will be +5% of L dimension.

Characteristic

Many types are available to meet various types of application.


Application

Instruments / Control boards / Machine tools / Home appliances / Medical instruments / Furniture / Office utilities, etc.

Specification

No waterproof ability because it is made by continuous foaming.
Please be aware that there may be joints and steps on the product.

L=ご希望の長さに切断いたします。(テープはB寸法の面に付いています。)
L: Please specify when ordering. (Tape shall be set on the B-surface.)



●納期についてはご相談ください。
Please contact us for the lead time.

寸法・仕様表 Size List & Specification テープ付 With Tape

※テープ付きは品番の後に T がつきます。
Model no. with T on this list means gasket with tape.

寸法・仕様表 Size List & Specification テープなし Without Tape

型番 Model No.	A	B	価格(円 /1m) Price (yen)
TM-131-1	3	12	¥240
TM-131-2		15	¥260
TM-131-3		20	¥260
TM-131-4		25	¥290
TM-131-5		30	¥310
TM-131-7	5	10	¥260
TM-131-8		15	¥260
TM-131-9		20	¥290
TM-131-10		30	¥365
TM-131-11	7	40	¥495
TM-131-13		15	¥290
TM-131-14		20	¥335
TM-131-15		30	¥475
TM-131-16	8	8	¥260
TM-131-17		10	¥275
TM-131-18		12	¥290
TM-131-19	10	15	¥310
TM-131-20		20	¥365
TM-131-21		25	¥505
TM-131-22		30	¥600
TM-131-23		35	¥695
TM-131-24		40	¥805
TM-131-25		40	¥925
TM-131-26	12	12	¥370
TM-131-27		15	¥435
TM-131-28		20	¥565
TM-131-32	15	15	¥550
TM-131-33		20	¥695
TM-131-34		25	¥875
TM-131-35		30	¥1,045
TM-131-37	20	20	¥925
TM-131-38		25	¥1,155
TM-131-39		30	¥1,390
TM-131-41		40	¥1,850

型番 Model No.	A	B	価格(円 /1m) Price (yen)
TM-131-1T	3	12	¥390
TM-131-2T		15	¥390
TM-131-3T		20	¥390
TM-131-4T		25	¥390
TM-131-5T		30	¥410
TM-131-7T	5	10	¥400
TM-131-8T		15	¥400
TM-131-9T		20	¥430
TM-131-10T		30	¥530
TM-131-11T	7	40	¥680
TM-131-13T		15	¥430
TM-131-14T		20	¥490
TM-131-15T		30	¥680
TM-131-16T	8	8	¥390
TM-131-17T		10	¥410
TM-131-18T		12	¥425
TM-131-19T	10	15	¥450
TM-131-20T		20	¥525
TM-131-21T		25	¥680
TM-131-22T		30	¥780
TM-131-23T		35	¥855
TM-131-24T		40	¥990
TM-131-25T		40	¥1,140
TM-131-26T	12	12	¥525
TM-131-27T		15	¥600
TM-131-28T		20	¥750
TM-131-32T	15	15	¥705
TM-131-33T		20	¥860
TM-131-34T		25	¥1,070
TM-131-35T		30	¥1,290
TM-131-37T	20	20	¥1,120
TM-131-38T		25	¥1,420
TM-131-39T		30	¥1,710
TM-131-41T		40	¥2,285

特注品のご相談承ります Please contact us for custom-made.