

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300080212](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change C-Size Single-Ended Cordset, 12 Poles, Female (90°) to Pigtail, 16 AWG, PVC Cable, 1.83m (6.0') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [130008](#)
Connector End A Mini-Change
Connector End B Pigtail
IP Rating IP67
Material - Contact Brass
Overview [Brad Mini-Change Connectors](#)
Product Name Mini-Change
Protocol DeviceNet
Region America
Type Single Ended
UPC 78678844112

Physical

Cable Diameter 18.03mm (.710")
Cable Length 1.83m (6.0')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut Black Epoxy Coated Zinc
Material - Plating Mating Gold
Orientation 90° to Pigtail
Poles 12
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 16
Wire/Cable Type ST00W

Electrical

Current - Maximum per Contact 5.0A
Voltage - Maximum 600V

Material Info

Engineering Number 302001A01F060

Reference - Drawing Numbers

Sales Drawing SD-130008-017



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130008](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION