

WARDING & NEEDLE FILES



Warding file -
Flat second cut, square

Item Number		i	
T0120 1	100mm 4"		6



Warding file -
Flat second cut, tapered

Item Number		i	
T0120 2	100mm 4"		6



Warding file -
Half round second cut

Item Number		i	
T0120 3	100mm 4"		6



Warding file -
Round second cut

Item Number		i	
T0120 4	100mm 4"		6



Warding file -
Square second cut

Item Number		i	
T0120 5	100mm 4"		6



Warding file -
Triangular second cut

Item Number		i	
T0120 6	100mm 4"		6



Warding file set -
6 Piece

Item Number		i	
T0120P	100mm 4"		3



Warding file set -
4 Piece

Item Number		i	
T0119	100mm 4"		3



Needle file set - 6 Piece

Item Number		i	
T0124P			3

- Brass chuck securely grips the needle file shaft for safe use



Needle file handle

Item Number			
T0071	95mm 3 3/4"		6

HAMMERS

- Drop forged high carbon steel head - hardened & tempered for superior strength and durability
- Black lacquered to protect against corrosion
- Tough hickory shaft for durability
- Ball pein for setting rivets



Ball pein hammers

Item Number			
T4208H 08	227g 1/2 lb		3
T4208H 16	454g 1 lb		3
T4208H 24	682g 1 1/2 lb		3
T4208H 32	908g 2 lb		3

- Drop forged high carbon steel head - hardened & tempered for superior strength and durability
- Black lacquered to protect against corrosion
- Traditional ash shaft for strength



Engineer's hammer -
French pattern

Item Number			
356002	300g 10 1/2 oz		12

- Drop forged high carbon steel head - hardened & tempered for superior strength and durability
- Black lacquered to protect against corrosion
- Traditional ash shaft for strength



Engineer's hammers -
German pattern

DIN 1041

Item Number			
T4227A 0100	100g 3 1/2 oz		12
T4227A 0200	200g 7 oz		12
T4227A 0300	300g 10 1/2 oz		12
T4227A 0500	500g 17 1/2 oz		12
T4227A 1000	1000g 35oz		12

PUNCHES

- Hardened carbon steel with gun metal finish for protection
- Knurled shaft for grip



Centre punch - Round 10mm

Item Number			
T3307P	100mm 4"		12

- High quality chrome vanadium steel hardened for durability



Centre punch - Octagonal 10mm

Item Number			
T3319	150mm 6"		6

- High quality chrome vanadium steel hardened for durability



Centre punch - Octagonal 12mm

Item Number			
T3326	120mm 4 3/4"		3